

Software - VISU+ 2 - 2988544

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Development license for Visu+ projects.

Your advantages

- Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- Access protection with user management



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356479677
Weight per Piece (excluding packing)	78.900 g
Custom tariff number	85234910
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

License information

Intended use for the software	Visualization
Type of license	Development license

Functions

Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server

Software - VISU+ 2 - 2988544

Technical data

Functions

	FDA CFR 21 Part 11 compatible
Expanded functionality	Statistical alarm function
	Web client capability
	Redundancy function
	Networking
	Visu+ as OPC server (DA & UA)
Integrated function	Advanced alarm management with SMS, FAX, e-mail and voice mail function
	SCADA system
	OPC client
	Trending
	Alarming
	Visual Basic
	Structured text
	Multi-user capability
	Programming interface
	Online configuration
	Password protection

Hardware requirements

Hard disk	min. 1 GByte (recommended: 2 GB)
RAM	min. 512 Mbyte (Recommended: 1 GByte)
CPU	Pentium/Celeron, 1.6 GHz
Optical drive	DVD-ROM
Monitor resolution	XGA (1024 x 768)
Operating equipment	Keyboard, mouse

Software requirements

Operating system	Windows® XP (SP3)
	Windows® Vista Business
	Windows® 7 Professional SP1 (32-Bit/64-Bit)
	Windows® 7 Ultimate SP1 (32-Bit/64-Bit)
	Windows® 8 Professional (32-Bit/64-Bit)
	Windows® 8 Enterprise (32-Bit/64-Bit)
	Windows® Server 2003
	Windows® Server 2008
	Windows® Server 2008 R2
	Windows® 10 (32-Bit/64-Bit)
Languages supported	German, English, French, Italian
Supported browsers	Internet Explorer 5.5 or higher

Software - VISU+ 2 - 2988544

Classifications

eCl@ss

eCl@ss 4.0	27338000
eCl@ss 4.1	27338000
eCl@ss 5.0	27242500
eCl@ss 5.1	27242500
eCl@ss 6.0	27242500
eCl@ss 7.0	27242502
eCl@ss 8.0	27242502
eCl@ss 9.0	27242502

ETIM

ETIM 2.0	EC001416
ETIM 3.0	EC001416
ETIM 4.0	EC001416
ETIM 5.0	EC001416
ETIM 6.0	EC001416
ETIM 7.0	EC001416

UNSPSC

UNSPSC 6.01	43163005
UNSPSC 7.0901	43232404
UNSPSC 11	43163005
UNSPSC 12.01	43232404
UNSPSC 13.2	43231507
UNSPSC 18.0	43231507
UNSPSC 19.0	43231507
UNSPSC 20.0	43231507
UNSPSC 21.0	43231507