

## Tool bag, equipped - TOOL-WRAP - 1212505

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Tool carry case wrap, equipped with: cable cutter, diagonal cutter, combination and needle-nose pliers  
VDE screwdriver bladed: 0.4x2.5/0.5x3.0/1.0x4.0/1.0x5.5 crosshead: PHO/PH1/PH2  
Voltage tester

### Your advantages

- Rugged and heavy-duty tool bags
- Universal tool sets, with cutting, stripping, crimping, and testing tools from the TOOL fox tool range

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 528412
GTIN	4046356528412
Weight per Piece (excluding packing)	2,500.000 g
Custom tariff number	82060000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	520 mm
Width (a)	250 mm
Height (c)	290 mm

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Articles in set

Diagonal cutter - CUTFOX-S VDE - 1212207



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested

## Tool bag, equipped - TOOL-WRAP - 1212505

### Articles in set

---

#### Cable-cutting tool - CUTFOX 16 VDE - 1212126



Cable cutter, precision blade with macro-notching, for copper and aluminum up to 50 mm<sup>2</sup>, VDE 1000 V AC/1500 V DC tested

---

#### Tool - UNIFOX-C VDE - 1212202



Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm

---

#### Tool - UNIFOX-P VDE - 1212204



Needle-nose pliers with blade, notched grip area, VDE 1000 V AC/1500 V DC tested

---

#### Screwdriver - SZS 0,4X2,5 VDE - 1205037



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

---

#### Screwdriver - SZS 0,5X3,0 VDE - 1207404



Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip

---

## Tool bag, equipped - TOOL-WRAP - 1212505

### Articles in set

Screwdriver - SZS 1,0X4,0 VDE - 1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZS 1,0X6,5 VDE - 1205079



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZK PH0 VDE - 1205147



Screwdriver, PH crosshead, VDE insulated, size: PH 0 x 80 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZK PH1 VDE - 1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZK PH2 VDE - 1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

---

# Tool bag, equipped - TOOL-WRAP - 1212505

## Articles in set

Voltage tester - DUSPOL EXPERT - 1209091



Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65

Tool bag, unequipped - TOOL-WRAP EMPTY - 1212501



Wrap-up tool bag, unequipped

## Classifications

### eCl@ss

eCl@ss 10.0.1	21045003
eCl@ss 4.0	21043000
eCl@ss 4.1	21043000
eCl@ss 5.0	21049000
eCl@ss 5.1	21049000
eCl@ss 6.0	21049000
eCl@ss 7.0	21045003
eCl@ss 8.0	21045003
eCl@ss 9.0	21045003

### ETIM

ETIM 3.0	EC000149
ETIM 4.0	EC000149
ETIM 5.0	EC000149
ETIM 6.0	EC000149
ETIM 7.0	EC000149

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27113201
UNSPSC 18.0	27113201

# Tool bag, equipped - TOOL-WRAP - 1212505

## Classifications

### UNSPSC

UNSPSC 19.0	27113201
UNSPSC 20.0	27113201
UNSPSC 21.0	27113201

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01750
-----	---	--------------------------