

Roll printer starter set - THERMOMARK ROLL KIT-GH - 5146769

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Printing set, consisting of THERMOMARK ROLL roll printer, CLIP-PROJECT PROFESSIONAL software, 50 m ink ribbon and 2500 labels for device marking


Product Description

The THERMOMARK ROLL processes material off the roll and continuous media. You can easily create high-quality printed labels and markers.

Your advantages

- ✓ The THERMOMARK ROLL prints marking material in roll format. For applications in terminal, wire, cable, equipment, and plant marking.
- ✓ Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- ✓ Fast, high-quality, and durable printing
- ✓ Easy and intuitive operation via touch screen entry
- ✓ Easy and intuitive operation via touch color display
- ✓ Easy and flexible control by means of the multilingual CLIP PROJECT planning and marking software. With the option of direct entry or import of printing information from various data sources
- ✓ USB and Ethernet connections

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 724531
GTIN	4046356724531
Weight per Piece (excluding packing)	6,180.000 g
Custom tariff number	84433210
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length	320 mm
Height	189 mm
Width	253 mm

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC

Roll printer starter set - THERMOMARK ROLL KIT-GH - 5146769

Technical data

Connection data

Additional text	50 Hz ... 60 Hz
-----------------	-----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	24190100
eCl@ss 4.1	24190100
eCl@ss 5.0	24321100
eCl@ss 5.1	24321100
eCl@ss 6.0	19140100
eCl@ss 7.0	19140190
eCl@ss 8.0	19140190
eCl@ss 9.0	19140190

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000005
ETIM 5.0	EC001672
ETIM 6.0	EC001672
ETIM 7.0	EC001672

UNSPSC

UNSPSC 6.01	27121706
UNSPSC 7.0901	27121706
UNSPSC 11	27121706
UNSPSC 12.01	27121706
UNSPSC 13.2	43212110
UNSPSC 19.0	43212110

Approvals

Approvals

Approvals

EAC

Roll printer starter set - THERMOMARK ROLL KIT-GH - 5146769

Approvals

Ex Approvals

Approval details

EAC		RU *- DE.A*30.B.02513
-----	--	--------------------------

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printer for printing product groups TML..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP..., EMLF..., PML..., and PMM..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110 BU - 0829544



Ink ribbon, width: 110 mm, color: blue

Ink ribbon - THERMOMARK-RIBBON 110 GN - 0829542



Ink ribbon, width: 110 mm, color: green

Ink ribbon - THERMOMARK-RIBBON 110 RD - 0829543



Ink ribbon, width: 110 mm, color: red

Roll printer starter set - THERMOMARK ROLL KIT-GH - 5146769

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-EML-HT - 0800342



Ink ribbon, for roll printer for printing product group EML-HT..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, for roll printer for printing product group WMS... (black), width: 110 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), width: 64 mm, color: white

Planning and marking software

Roll printer starter set - THERMOMARK ROLL KIT-GH - 5146769

Accessories

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

Printing system accessories

Cutter - THERMOMARK ROLL-CUTTER - 5146422



Cutter, for the THERMOMARK ROLL, cutter width: 110 mm, suitable for: labels, continuous media up to 110 mm wide, PMM continuous media up to 50.1 mm in diameter, TMT continuous media, and EMT (EX15)R

Cutter - THERMOMARK ROLL-CUTTER/P - 5146435



Perforation cutter, for the THERMOMARK ROLL, cutter width: 60 mm, suitable for: WMS continuous media up to 25.8 mm in diameter, TMT continuous media, and EMT (EX15)R

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Roll printer starter set - THERMOMARK ROLL KIT-GH - 5146769

Accessories

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

Transport case - TL CASE - 0800613



Transport case for THERMOMARK printer, rounded profile case with aluminum frame
