

Connector - C-SCF 1/2,8X0,5 - 3240152

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Slip-on sleeve, non-insulated, 0.5 ... 1 mm², 2.8 x 0.5

Your advantages

- ✓ They round out the product range in terms of connectors
- ✓ The uninsulated slip-on sleeves and flat plugs are made from electrolytically tin-plated brass

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 453691
GTIN	4046356453691
Weight per Piece (excluding packing)	0.230 g
Custom tariff number	85369010
Country of origin	Belgium

Technical data

Dimensions

Length (b)	14.5 mm
Width (a)	2.8 mm
Maximum stripping length	7 mm
Material thickness (g)	0.3 mm

Ambient conditions

Ambient temperature (operation)	110 °C
---------------------------------	--------

General

Color	silver
Stripping length	7 mm

Connector - C-SCF 1/2,8X0,5 - 3240152

Technical data

General


Components	halogen-free
Material	Brass
Insulating material	nicht zutreffend
Coating	tin-plated

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Connector - C-SCF 1/2,8X0,5 - 3240152

Classifications

eCl@ss

eCl@ss 4.0	27060700
eCl@ss 4.1	27060700
eCl@ss 5.0	27400200
eCl@ss 5.1	27400200
eCl@ss 6.0	27400200
eCl@ss 7.0	27400204
eCl@ss 8.0	27400204
eCl@ss 9.0	27400212

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 5.0	EC000516
ETIM 6.0	EC001059
ETIM 7.0	EC001059

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121707
UNSPSC 19.0	27121707

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	--	---------------

Connector - C-SCF 1/2,8X0,5 - 3240152

Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-SC 1,5 - 1212048



Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.1 - 1.5 mm², B crimp

Crimping pliers - CRIMPFOX-SC 1,5-M - 1212725



Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.1 - 1.5 mm², B crimp

Crimping pliers - CRIMPFOX-SC 6 - 1212050



Crimping pliers, for uninsulated slip-on sleeves 2.8, 4.8, and 6.3 mm, 0.5 - 6 mm², B crimp
