

Stripping tool - WIREFOX-D CX-5 - 1212167


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Stripping tool for coaxial cables of Ø 2.5 ... 7.6 mm, 3-level, strip-off dimensions 5.5 and 5.5 mm

Your advantages

- Large selection of precision stripping tools
- The right tool for every application



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 454353
GTIN	4046356454353
Weight per Piece (excluding packing)	78.000 g
Custom tariff number	82032000
Country of origin	Sweden
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	90 mm
Width (a)	25.5 mm
Height (c)	37.5 mm
Cable diameter	2.5 mm ... 7.6 mm
Stripping length	5.5 mm

General

Color	black
Type of contact	Coaxial
Weight	90 g
Min. cross section	0 mm ²
Max. cross section	0 mm ²

Stripping tool - WIREFOX-D CX-5 - 1212167

Technical data

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043706
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043706
eCl@ss 8.0	21043706
eCl@ss 9.0	21043706

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000163
ETIM 5.0	EC000163
ETIM 6.0	EC002109
ETIM 7.0	EC002109

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111518
UNSPSC 18.0	27111510
UNSPSC 19.0	27111510
UNSPSC 20.0	27111510
UNSPSC 21.0	27111510

Approvals

Approvals

Approvals

EAC

Stripping tool - WIREFOX-D CX-5 - 1212167

Approvals

Ex Approvals

Approval details

EAC



RU x-
DE.xx08.B.02974

Accessories

Accessories

Knife

Spare knife - WIREFOX-D CX-5/SB - 1212307



Spare knife for WIREFOX-D CX-5, strip-off dimensions 5.5 + 5.5 mm