

Industrial
Equipment
Manufacturing

Edge
Solution Ready
Package


Secured Edge Analyzer

Intelligent Platform with Azure IoT Edge &
WISE-PaaS/EdgeLink

ESRP-CSS-UNO Series



- Extends cloud intelligence and analytics to edge devices
- Boosts productivity and response times with data insights
- Offers secure cloud communication and edge intelligence
- WISE-PaaS/EdgeLink supports more than 200 PLC device



ESRP-CSS-UNO2271

ESRP-CSS-UNO2372

ESRP-CSS-UNO1372



ESRP-CSS-UNO2484



Data Filter

Supports Numerous IoT Modules

Machine Learning

Stream Analysis

Database Localization

Microsoft
Azure

Certified

WISE-PaaS/EdgeLink

ADVANTECH

Enabling an Intelligent Planet

POWERED BY
ADVANTECH
WISE-PaaS

Edge Solution-Ready Package

ESRP-CSS-UNO2484, ESRP-CSS-UNO2372

ESRP-CSS-UNO1372, ESRP-CSS-UNO2271

Extends cloud intelligence and analytics to edge devices

IoT solutions, such as stream analytics, machine learning, image recognition, and other high-value AI modules, deployed from the cloud to the edge to support diverse applications.

Boosts productivity and response times with data insights

Local data processing enables immediate decision-making and reduces bandwidth costs by minimizing the data transmitted from local devices to the cloud.

Offers secure cloud communication and edge intelligence

The inclusion of Azure IoT Edge Security Daemon and onboard TPM 2.0 increases device security while a SSL ensures connectivity between the cloud and intelligent edge.

WISE-PaaS/EdgeLink supports more than 200 PLC device

Edgelink supports more than 200 PLC device for collecting data from devices, and features plug-and-play functionality which reduce software development time. Eliminate the gap between OT and IT.

Intelligent Platform with Azure IoT Edge & WISE-PaaS/EdgeLink				
Part Number	ESRP-CSS-UNO2484	ESRP-CSS-UNO2372	ESRP-CSS-UNO1372	ESRP-CSS-UNO2271
Operating System	AdvLinuxTU			
Application Software	Microsoft Azure IoT Edge Engine			
Control Software	WISE-PaaS/EdgeLink 8000 tags	WISE-PaaS/EdgeLink 5000 tags	WISE-PaaS/EdgeLink 5000 tags	WISE-PaaS/EdgeLink 3000 tags
CPU	Intel® Core™ i5-7300U (2.6 GHz)	Intel® Celeron™ J1900 (2.0 GHz)	Intel® Celeron™ J1900 (2.0 GHz)	Intel® Atom™ E3825 (1.33 GHz)
Memory	8 GB DDR4	4 GB DDR3L	4 GB DDR3L	4 GB DDR3L
Display Size/Type	1 x HDMI, supports 1920x1080 @ 60Hz 1 x DP, supports 3840x2160 @ 30Hz			
Storage	32 GB SSD	64 GB SSD	32 GB SSD	32 GB eMMC
Expansion Slots	1 x Full-size mPCIe slot			
Network (LAN)	4 x RJ45	2 x RJ45 10/100/1000 Mbps IEEE 802.3u 1000Base-T Fast Ethernet		
I/O	4 x RS-232/422/485 4 x USB 3.0	4 x RS232/422/485 1 x USB 3.0, 3 x USB 2.0	4 x RS-232/422/485 1 x USB 3.0, 3 x USB 2.0	2 x RS 232/422/485 1 x USB 3.0
Power Input (Voltage)	10 ~ 36 V _{DC}			
Operating Temperature	-20 ~ 60 °C (-4 ~ 140 °F)			0 ~ 50 °C (32 ~ 122 °F)
Storage Temperature	40 ~ 85 °C (-40 ~ 185 °F)			-20 ~ 70 °C (-4 ~ 158 °F)
Dimensions (W x D X H)	200 x 140 x 40 mm (7.8" x 5.6" x 1.6" in)	150 x 105 x 35mm (5.8" x 4.2" x 1.4")	65 x 105 x 150mm (2.6" x 4.1" x 5.9" in)	100 x 70 x 65 mm (3.9" x 2.8" x 2.6" in)
Certification	CE, FCC Class A, UL, CCC, BSMI			

Ordering Information

ESRP-CSS-UNO2484	Cloud-Ready Secured Azure IoT Edge Gateway with WISE-PaaS/Edgelink Linux 8000 tags UNO-2484G-7531AE, 8 GB RAM, 32 GB SSD, AdvLinuxTU
ESRP-CSS-UNO2372	Cloud-Ready Secured Azure IoT Edge Gateway with WISE-PaaS/Edgelink Linux 5000 tags UNO-2372G-J021AE, 4 GB RAM, 64 GB SSD, AdvLinuxTU
ESRP-CSS-UNO1372	Cloud-Ready Secured Azure IoT Edge Gateway with WISE-PaaS/Edgelink Linux 5000 tags UNO-1372G-J021AE, 4 GB RAM, 32 GB SSD, AdvLinuxTU
ESRP-CSS-UNO2271	Cloud-Ready Secured Azure IoT Edge Gateway with WISE-PaaS/Edgelink Linux 3000 tags UNO-2271G-E023AE, 4 GB RAM, 32 GB eMMC, AdvLinuxTU