



# Technical Specification

## 30m + 3m Anti-Twist Reverse Reel

### OATRU3013FL3IP




### Features

- » Innovative reverse reel with pull-out socket
- » Safety thermal cut-out
- » Fold-out speed wind handle
- » Power LED indicator
- » IP54 rated weatherproof socket
- » IP rated socket ideal for use with pressure washers and in damp conditions

### Description

This reverse reel with pull out socket and anti-twist design is an innovative solution that keeps cables from getting tangled. Using the wall mount bracket, fix the reel to the wall close to the power outlet and extend the power socket closer to the required area. The compact design is perfect for the home, garden and light industrial use. Using highly visible green cable, this 'reverse' reel provides an IP54 rated weatherproof 13 amp socket outlet. The drum includes an LED indicator and has a built-in safety thermal cut out for protection against overloading when fully reeled. Supplied with wall mount bracket.

### Line Diagrams



### Technical Specifications

<b>Standards</b>	BS EN 61242. ASTA Approved
<b>Maximum Load</b>	720W/240V - Fully Wound 3120W/240V - Fully Unwound
<b>Switch</b>	Double Pole
<b>Cable length</b>	30 + 3m
<b>Cable Size</b>	Cable Size - 1.25mm <sup>2</sup> (H05VV-F)



Lic 940



## Product Information

<b>Part No</b>	OATRU3013FL3IP-PX	<b>Qty</b>	1
<b>Type</b>	Anti-Twist Reverse Reel	<b>Shipping Carton Info (m)</b>	H:0.31 x W:0.3 x D:0.33
<b>Cable Type</b>	PVC	<b>CBM (m<sup>3</sup>)</b>	0.031
<b>Cable Length (m)</b>	30 + 3m	<b>G.W (kg)</b>	6.1
<b>Amp</b>	13	<b>EAN Barcode</b>	5015056538952
<b>Product Dimensions (cm)</b>	H:28.6 x W:28.2 x D:27.3	<b>ITF Barcode</b>	05015056540078

## Product Range

Product Image	Cat No	Description	Length (m)	Sockets	Amps
	CMU10134SL	Cassette Reel	10m	4 Sockets	13
	HMU15134SL	Case Reel	15m	4 Sockets	13
	OMU25134SL	Open Reel	25m	4 Sockets	13
	OLU50134SL	Open Reel	50m	4 Sockets	13
	OTLU40134SL	Heavy Duty Metal Open	40m	4 Sockets	13
	OMU2513FL3IP	Reverse Open Reel	25+3m	1 Socket	13
	OATRU3013FL3IP	Anti-Twist Reverse Reel	30+3m	1 IP54 Socket, + LED	13
	OATFU30134SL	Anti-Twist Fixed Socket	30m	4 Sockets, Switch + LED	13
	OMU25132USL	Open Reel with USB Charging	25m	2 Sockets, Switched + USB	13

Masterplug are proud to offer a 5 year warranty on its range of Pro-XT portable power products from the date of purchase.

Please see our website [www.masterplug-proxt.com](http://www.masterplug-proxt.com) for more details.

### UK Sales & Distribution Centre

Luceco plc  
Stafford Park 1, Telford, Shropshire, England, TF3 3BD  
Tel: +44 (0) 1952 238 100 Fax: +44 (0) 1952 238 180  
Email: [sales@masterplug.com](mailto:sales@masterplug.com)

[www.masterplug-proxt.com](http://www.masterplug-proxt.com)

Tech Help Line: (UK) 03300 249 279  
(Non UK) +44(0) 1952 238 100



**POWER  
AT WORK**

