

You can view this page in:

EN DE SV FI CS DA EL ES FR HU IT JA KO NL NO PL PT RU SK
TR ZH

Detailed information for: TS 25/12-24 C

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

TS 25/12-24 C

General Information

| | |
|-------------------------------|---|
| Extended Product Type: | TS 25/12-24 C |
| Product ID: | 2CSM251043R0811 |
| EAN: | 8012542928508 |
| Catalog Description: | TS 25/12-24 C Safety isolating transformer |
| Long Description: | TS-C are ideal for supplying permanent power to meters, auxiliary electronic devices and circuits with very low safety voltage (SELV) for bathrooms and showers, lighting, fountains, electro-medical devices and suchlike. |

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Command and Signalling devices » Bells and safety transformers

Ordering

| | |
|--------------------------------|---------------|
| E-Number (Sweden): | 5208116 |
| EAN: | 8012542928508 |
| Minimum Order Quantity: | 1 piece |
| Customs Tariff Number: | 85043121 |

Dimensions

| | |
|------------------------------------|----------|
| Product Net Width: | 70 mm |
| Product Net Height: | 0.085 m |
| Product Net Length: | 44 mm |
| Product Net Depth / Length: | 0.120 m |
| Product Net Weight: | 0.945 kg |

Container Information

| | |
|--|---------------|
| Package Level 1 Units: | 1 piece |
| Package Level 1 Width: | 0.095 m |
| Package Level 1 Height: | 0.077 m |
| Package Level 1 Depth / Length: | 0.216 m |
| Package Level 1 Gross Weight: | 0.92 kg |
| Package Level 1 EAN: | 8012542928508 |

Environmental

| | |
|---------------------|---|
| RoHS Status: | Following EU Directive 2002/95/EC August 18, 2005 and amendment |
|---------------------|---|

Additional Information

| | |
|--------------------------|------|
| Options Provided: | None |
|--------------------------|------|

| | |
|---|------------------------------|
| Output Current Maximum (I_{out}): | 1,04 A |
| Power Loss: | Maximum 4 W |
| Power Supply: | 25 V·A |
| Primary Voltage: | 230 V |
| Product Main Type: | TS-C |
| Product Name: | Safety isolating transformer |
| Rated Operational Voltage: | 230 V AC |
| RoHS Date: | 20/04/2006 0.00.00 |
| Secondary Voltage: | 12-24 V AC |

Certificates and Declarations (Document Number)

Data Sheet, Technical Information: [2CSC400002D0209](#)

Declaration of Conformity - CE: [2CSC446003D2701](#)

Environmental Information: [See RoHS Information](#)

Instructions and Manuals: [on the product body.](#)

RoHS Information: [2QD00031](#)

Classifications

ETIM 4: EC002048 - Current transformer

ETIM 5: EC002048 - Current transformer

ETIM 6: EC001547 - Bell transformer

ETIM 7: EC001547 - Bell transformer

Object Classification Code: T

WEEE Category: 5. Small Equipment (No External Dimension More Than 50 cm)



Contact us

Submit your inquiry and
we will contact you

CONTACT US

Or contact your [ABB Contact Center](#)

© Copyright 2019 ABB