

PRODUCT-DETAILS

# E2.2 W FP Iu=2000 4p HR HR

# E2.2 W FP Iu=2000 4p HR HR



## General Information

Extended Product Type	E2.2 W FP Iu=2000 4p HR HR
Product ID	1SDA073910R1
EAN	8015644778439
Catalog Description	E2.2 W FP Iu=2000 4p HR HR
Long Description	FIXED PART WITHDRAWABLE FOR C.BREAKER SACE EMAX2 E2.2 2000 FOUR-POLE WITH REAR HORIZONTAL TERMINALS

## Ordering

EAN	8015644778439
Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

## Dimensions

Product Net Width	407 mm
Product Net Height	425 mm
Product Net Depth / Length	383 mm
Product Net Weight	44 kg

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	570 mm
Package Level 1 Height	610 mm
Package Level 1 Depth / Length	615 mm
Package Level 1 Gross Weight	49 kg
Package Level 1 EAN	8015644778439

### Additional Information

Current Type	AC
Electrical Durability	2000 cycle
Mechanical Durability	25000 cycle 60 cycles per hour
Neutral Pole Current ([% Iu])	100 %
Number of Poles	4
Product Main Type	SACE Emax 2
Product Name	Fixed Part
Product Type	Fixed Part
Rated Current (I <sub>n</sub> )	2000 A
Rated Voltage (U <sub>r</sub> )	690 V
Rated Impulse Withstand Voltage (U <sub>imp</sub> )	acc. to IEC 60947-2 12 kV
Rated Insulation Voltage (U <sub>i</sub> )	AC 1000 V
Rated Operational Voltage	690 V AC
Rated Uninterrupted Current (I <sub>u</sub> )	2000 A
Standards	IEC
Sub-type	E2.2
Terminal Connection Type	Rear flat Horizontal
Version	W FP

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC200023D0204
Declaration of Conformity - CE	1SDL000165R0020
Environmental Information	Not Available
Instructions and Manuals	1SDH001000R0820

### Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC002043 - Chassis part power circuit breaker
ETIM 7	EC002043 - Chassis part power circuit breaker
Object Classification Code	Q
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

## Categories

---

Low Voltage Products and Systems → Circuit Breakers → Air Circuit Breakers → Emax 2

