



CorePro LEDbulbs

CorePro LEDbulb ND 11-75W A60 B22 827

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost. The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Wattage Equivalent	
Cap-Base	B22 [B22]		75 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	15000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Power Factor (Nom)	0.5
Technical Type	11-75W	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	200 °	Controls and Dimming	
Luminous Flux (Nom)	1055 lm	Dimmable	No
Color Designation	Warm White (WW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2700 K	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	95.00 lm/W	Approval and Application	
Color Consistency	<6	Energy Efficiency Label (EEL)	A+
Color Rendering Index (Nom)	80	Energy Consumption kWh/1000 h	11 kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Data	
Operating and Electrical		Full product code	871869657761500
Input Frequency	50 to 60 Hz	Order product name	CorePro LEDbulb ND 11-75W A60 B22 827
Power (Nom)	11 W		
Lamp Current (Nom)	95 mA		

CorePro LEDbulbs

EAN/UPC - Product	8718696510049
Order code	929001234002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	929001234002
Net Weight (Piece)	0.080 kg


Dimensional drawing




Entrybulb 230V 10.5W-75W 2700K B22 ND

Product	D	C
CorePro LEDbulb ND 11-75W A60 B22 827	60 mm	110 mm


Photometric data



CorePro LEDbulb ND 11-75W A60




CorePro LEDbulb ND 11-75W A60



SDPO_LED Bulb_0021-Spectral Power distribution

CorePro LEDbulbs

Lifetime



LEDbulb 100W E27 840 FR A60

LEDbulb 100W E27 840 FR A60

