

Special function module - EEM-MEMO-MA600 - 2901370

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Storage module for intermediate storage of values for EEM-MA600



Your advantages

- Stores the last ten alarms together with the time and date
- Stores the real and reactive power, e.g., for 31 days with a ten-minute synchronization pulse

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 585798
GTIN	4046356585798
Weight per Piece (excluding packing)	130.900 g
Custom tariff number	90303100
Country of origin	Hungary
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	22.5 mm
Height	65 mm
Depth	48 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 55 °C (14 °F to 131 °F)
Ambient temperature (storage/transport)	-20 °C ... 85 °C (-4 °F ... 185 °F)
Max. permissible relative humidity (operation)	≤ 95 %

Special function module - EEM-MEMO-MA600 - 2901370

Technical data

Ambient conditions

Max. salt spray content	≤ 2.5 %
-------------------------	---------

Input data

Description of the input	Optocoupler input
Number	1
Voltage input signal	10 V DC ... 30 V DC
Input pulse length	≥ 1 s
Peak offstate voltage	30 V DC
Memory size	512 kByte

General

Supply voltage	9 V (via EEM-MA600)
Color	black
Conformance	CE-compliant
Test voltage	3.5 kV AC (50 Hz, 1 min.)

Standards and Regulations

Conformance	CE-compliant
UL, USA/Canada	UL 61010-1
	CSA-C22.2 No. 61010-1
	cULus

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27371100
eCl@ss 4.1	27371100
eCl@ss 5.0	27371800
eCl@ss 5.1	27371800
eCl@ss 6.0	27149200
eCl@ss 7.0	27149223
eCl@ss 8.0	27149223
eCl@ss 9.0	27142336

ETIM

ETIM 4.0	EC002295
ETIM 5.0	EC002295
ETIM 6.0	EC002295
ETIM 7.0	EC002295

Special function module - EEM-MEMO-MA600 - 2901370

Classifications

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	32101606
UNSPSC 19.0	32101606