

# BJMI10-10



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Jumper Bars

## General Information

|                               |   |
|-------------------------------|---|
| <b>Extended Product Type:</b> | BJMI10-10   |
| <b>Product ID:</b>            | 1SNA176679R1000   |
| <b>EAN:</b>                   | 3472591766790   |
| <b>Catalog Description:</b>   | BJMI10-10 POLES Jumper Bars   |
| <b>Long Description:</b>      | - IP20 assembled screw jumper bars, - Perforated jumper bar with captive screws and spacers, - Allows the connection of consecutive blocks or not: remove unnecessary screw and spacer. |

## Ordering

|                                |          |
|--------------------------------|----------|
| <b>Minimum Order Quantity:</b> | 10 piece |
| <b>Customs Tariff Number:</b>  | 85369010 |

## Popular Downloads

|   |                                  |
|---|----------------------------------|
| <b>Data Sheet, Technical Information:</b> | 1SNC160001C0207-CH-J Accessories |
| <b>Instructions and Manuals:</b>          | 1SNC160001C0207-CH-J Accessories |

## Dimensions

|                            |      |
|----------------------------|------|
| <b>Product Net Weight:</b> | 27 g |
|----------------------------|------|

## Technical

|                                       |  |
|---------------------------------------|--|
| <b>Spacing:</b>                       | 10 mm  |
| <b>Function:</b>                      | Jumper Bars  |
| <b>Rated Current (I<sub>n</sub>):</b> | Main Circuit 57 A  |
| <b>Degree of Protection:</b>          | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20   |
| <b>Mounting on DIN Rail:</b>          | G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715<br>TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715<br>TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| <b>Suitable For:</b>                  | C10/10<br>M10/10<br>M10/10.ST-Sn   |

## Certificates and Declarations (Document Number)

|  |                                  |
|--|----------------------------------|
| <b>Declaration of Conformity - CE:</b> | 1SND225001C1009                  |
| <b>Instructions and Manuals:</b>       | 1SNC160001C0207-CH-J Accessories |
| <b>RoHS Information:</b>               | 1SND230492F0201                  |

## Classifications

|                                    |   |
|------------------------------------|---|
| <b>Object Classification Code:</b> | X   |
| <b>ETIM 4:</b>                     | EC000489 - Cross-connector for terminal block |
| <b>ETIM 5:</b>                     | EC000489 - Cross-connector for terminal block |
| <b>ETIM 6:</b>                     | EC000489 - Cross-connector for terminal block |

## Container Information

|  |               |
|--|---------------|
| <b>Package Level 1 Units:</b>          | 10 piece      |
| <b>Package Level 1 Width:</b>          | 155 mm        |
| <b>Package Level 1 Depth / Length:</b> | 200 mm        |
| <b>Package Level 1 Height:</b>         | 5 mm          |
| <b>Package Level 1 Gross Weight:</b>   | 0.27 kg       |
| <b>Package Level 1 EAN:</b>            | 3472591766790 |
| <b>Package Level 2 Units:</b>          | 200 piece     |
| <b>Package Level 2 Width:</b>          | 175 mm        |
| <b>Package Level 2 Depth / Length:</b> | 227 mm        |
| <b>Package Level 2 Height:</b>         | 130 mm        |
| <b>Package Level 3 Units:</b>          | 36000 piece   |
| <b>Product Packing Type:</b>           | Bag           |

