

6.6 ft. (2 m) HDMI to Mini DisplayPort Cable - 4K 30Hz

Product ID: HD2MDPMM2M



This 6.6 ft. HDMI® to Mini DisplayPort™ cable (male to male) lets you connect an HDMI video source, such as your laptop, desktop, Blu-ray™ player or camera, to a Mini DP monitor or display without the need for additional video cables and adapters.

Astonishing Picture Quality

With support for 4K at 30Hz, you get a sharp, crisp picture that's richer and more true-to-life than traditional HD, with far greater detail. The HDMI to Mini DisplayPort adapter cable delivers UHD content to your mDP display and supports 7.1 channel surround audio.

The video converter is also backward compatible with 1440p and 1080p displays, which makes it a great accessory to for your existing setup at home or in the office.

Clutter-Free Installation

At 6.6 ft. (2 m) in length, this HDMI to mDP cable delivers a direct connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation. For shorter installations, we also offer a 3.3 ft. (1 m) adapter cable, enabling you to choose the right cable length for your custom installation needs.

Convenient Connectivity

This active HDMI to Mini DP converter offers plug-and-play installation, providing a hassle-free setup with no software or drivers to install. The adapter cable is powered via a USB port, avoiding the need for external power adapters.

HD2MDPMM2M is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your HDMI computer to a Mini DisplayPort monitor
- Ideal for boardroom or office workstations
- View 4K video from your HDMI source on an mDP display

Features

- Reduce clutter with a cable and adapter in-one
- Active HDMI to Mini DisplayPort conversion transmits high-definition audio and video from your computer to a Mini DP monitor
- Delivers astonishing picture quality with support for video resolutions up to Ultra HD 4K
- Provides a convenient plug-and-play solution with no additional adapters required

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Audio	Yes
	AV Input	HDMI - 1.4
	AV Output	Mini-DisplayPort
	Chipset ID	MegaChips - STDP2600
Performance	Audio Specifications	Mini DisplayPort - 7.1 Channel Audio
	Supported Resolutions	Mini DisplayPort: 3840x2160 (4K) / 30Hz Additional resolutions and refresh rates may be supported
	Video Revision	HDMI 1.4
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - HDMI Male Input
	Connector B	1 - Mini DisplayPort Male Output
Environmental	Humidity	5%-90% RH (no condensation)
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 55°C (14°F to 131°F)
Physical Characteristics	Color	Black
	Material	Plastic
	Product Height	12.500
	Product Length	78.7 in [200 cm]
	Product Width	20.000
	Weight of Product	110.000
Packaging Information	Package Height	0.010
	Package Length	220.000
	Package Width	200.000
	Shipping (Package) Weight	120.000
What's in the Box	Included in Package	1 - HDMI to Mini DisplayPort Adapter Cable

Product appearance and specifications are subject to change without notice.