



CorePro LEDbulbs

CorePro LEDbulb ND 5.5-40W A60 B22 827

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost. The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General Information	
Cap-Base	B22 [B22]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	5.5-40W
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	200 °
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	5.5 W
Lamp Current (Nom)	55 mA


Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	6 kWh
Product Data	
Full product code	871869657765300
Order product name	CorePro LEDbulb ND 5.5-40W A60 B22 827

CorePro LEDbulbs

EAN/UPC - Product	8718696577653
Order code	929001233802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	929001233802
Net Weight (Piece)	0.076 kg



Dimensional drawing



Entrybulb 230V 6W-40W 470lm 2700K B22 ND


Product	D	C
CorePro LEDbulb ND 5.5-40W A60 B22 827	60 mm	110 mm

Photometric data



CorePro LEDbulb ND 5.5-40W A60


CorePro LEDbulb ND 5.5-40W A60




SDPO_LED Bulb_0021-Spectral Power distribution

CorePro LEDbulbs

Lifetime



LEDbulb 40W E27 830 FR A60



LEDbulb 40W E27 830 FR A60

