

## Wireless Access Point Enclosure - NEMA 4, Surface-Mount, PC Construction, 13 x 9 in.

MODEL NUMBER: EN1309N4



Protects your indoor or outdoor Wi-Fi access point against water, dust, rain, sleet, snow and ice, as well as theft, damage or tampering.

### Features

#### Wall-Mount Enclosure Secures and Organizes Your Router/Modem or Wireless Access Point

Protect your indoor or outdoor router/modem or Wi-Fi access point by installing it inside this SmartRack® NEMA 4 Wireless Access Point Enclosure made from impact-resistant UL 94 V-1 Classified PC plastic. It's ideal for offices, dorms, hotels, classrooms, retail locations and other indoor/outdoor areas where you need to keep Wi-Fi equipment secure, organized and out of the way.

#### Carries a NEMA 4 Rating for Protection Against Harsh Elements

The NEMA 4-rated enclosure supports indoor or outdoor use. It protects its contents against the ingress of water (including rain, sleet, snow, splashing water and hose-directed water), solid foreign objects (including falling dirt and windblown dust) and even ice forming on the outside of the enclosure.

#### Accommodates a Wide Range of Equipment, Including Cisco WAPs, up to 468 in.<sup>3</sup>

Though the EN1309N4 is designed specifically to protect Cisco Wi-Fi access points, it will also house most other equipment up to 468 cubic inches (7669 cubic centimeters). While rugged enough to keep your equipment safe inside, it's also transparent to wireless signals, ensuring strong Wi-Fi coverage. The polycarbonate plastic cover attaches to the enclosure with the included screws to protect the contents against theft or tampering.

#### Supports Wall- or Ceiling-Mounting to Best Fit Your Application

The EN1309N4 comes fully assembled and ready for horizontal or vertical mounting on a wall or ceiling with user-provided hardware. It is designed for Cisco WAPs, but the included universal T-bar bracket will accommodate a wide variety of equipment from other brands.

### Highlights

- Designed for Cisco WAPs, but accommodates equipment from most vendors
- NEMA 4 rating ensures protection against water, dust, rain, sleet, snow and ice
- Rugged polycarbonate housing protects router/modem/WAP from theft or tampering
- Transparent to wireless signals, ensuring an optimum Wi-Fi signal in all directions
- Comes fully assembled and ready for wall- or ceiling-mounting using included hardware

### Applications

- Protect a router/modem or wireless access point inside a classroom, office, hotel, store, dorm or other indoor space from damage, theft or tampering
- Protect outdoor equipment against water, dust, rain, sleet, snow and ice

### Package Includes

- NEMA 4 wireless access point enclosure, 13 x 9 in.
- (4) M4 screws
- (2) M6 screws, 1 in.
- (2) M6 trusshead screws, 0.25 in.
- (4) M6 flathead screws, 0.25 in.
- Cable tie
- (4) Nylon spacers
- T-bar bracket



- Installation guide

## Specifications

OVERVIEW	
UPC Code	037332217837
Rack Type	Enclosure
PHYSICAL	
Color	White
Maximum Device Depth (cm)	9.65
Maximum Device Depth (in.)	3.8
Maximum Device Depth (mm)	97
Rack Height	0U
Shipping Dimensions (hwd / cm)	35.71 x 25.10 x 13.90
Shipping Dimensions (hwd / in.)	14.06 x 9.88 x 5.47
Shipping Weight (kg)	1.90
Unit Dimensions (cm)	33.99 x 71.628
Unit Dimensions (hwd / cm)	33.99 x 71.628 x 10.6
Unit Dimensions (hwd / in.)	13.38 x 9.06 x 4.0
Unit Dimensions (in.)	13.38 x 9.06
Unit Weight (kg)	1.50
Unit Weight (lbs.)	3.3
SPECIAL FEATURES	
Built-in Cable Management	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>