

## USB-C to Gigabit Network Adapter, Thunderbolt 3 Compatibility - White

MODEL NUMBER: **U436-06N-GBW**



Connect the USB-C or Thunderbolt™ 3 port on your computer, laptop or smartphone to a wired Ethernet network. Access true Gigabit network speed without the expense and hassle of adding an internal Ethernet card to your device.

### Description

The U436-06N-GBW USB 3.1 Gen 1 Type-C to Gigabit Ethernet NIC Network Adapter allows USB Type-C or Thunderbolt™ 3 computers, laptops and smartphones without an NIC (Network Interface Controller) to connect to a network or the Internet using an Ethernet cable. It's a more convenient and less expensive way to connect to the network than opening your device and installing an internal Ethernet card. Connect the adapter's USB-C connector to your device's USB-C or Thunderbolt™ 3 port, and connect the adapter's RJ45 port to your network or Ethernet cable. Just plug and play with no drivers or external power supply needed. It's compact and lightweight for easy carrying in your laptop bag.

The USB 3.1 Gen 1 adapter supports full 10/100/1000 Mbps network speeds, allowing you to transfer a lot of data quickly and stream audio and video. Unlike traditional USB cables that can be attached only one way, the reversible USB Type-C male connector plugs into a USB or Thunderbolt™ 3 port in either direction for fast, fumble-free connection every time. Compliant with IEEE 802.3, 802.3u, 802.3ab and 802.3az standards. Supports 10/100/1000 auto-sensing, twisted-pair crossover detection, auto-correction and Wake-on-LAN power management. Compatible with Windows, Mac and Chromium operating systems. Backward compatible with previous USB versions.

### Features

#### Saves You Time and Money

- Connects USB Type-C or Thunderbolt™ 3 devices to a network or the Internet without buying and installing an internal Ethernet card
- Plug-and-play engineering—no drivers or external power supply necessary
- Compact and lightweight for easy carrying in your laptop bag

### Highlights

- Connects a USB Type-C or Thunderbolt™ 3 device to a wired Ethernet network
- Supports full 10/100/1000 Mbps network speeds
- Features reversible USB Type-C male plug on one end
- Compatible with Windows, Mac and Chromium operating systems
- Plug and play—no drivers or external power supply needed

### System Requirements

- Computer, tablet, laptop or smartphone with USB Type-C or Thunderbolt™ 3 port
- Windows, Mac or Chromium operating system

### Package Includes

- U436-06N-GBW USB 3.1 Gen 1 Type-C to Gigabit Ethernet NIC Network Adapter
- Quick Start Guide



### Excellent Speed and Versatile Performance

- Sustains full 10/100/1000 Mbps network speeds for fast data transfer
- Complies with IEEE 802.3, 802.3u, 802.3ab and 802.3az (Energy Efficient Ethernet) standards
- Supports 10/100/1000 auto-sensing, twisted-pair crossover detection, auto-correction and Wake-on-LAN
- Compatible with Windows, Mac and Chromium operating systems
- Also works with USB 3.0, USB 2.0 and USB 1.1 ports

### USB Type-C Male Connector

- Fumble-free reversible plug ensures fast, easy connection every time

## Specifications

OVERVIEW	
UPC Code	037332189240
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (1.2 Port)	No
PHYSICAL	
Cable Jacket Rating	VW-1
Color	White
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / in.)	4.70 x 4.00 x 0.80
Shipping Weight (lbs.)	0.08
Unit Dimensions (hwd / in.)	0.63 x 1.1 x 2.36
Unit Packaging Type	Box
Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.06



<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 158 F (0 to 70 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	3.1 BTU/Hr
Power Consumption (Watts)	1W Max
<b>COMMUNICATIONS</b>	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	RJ45 (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	No
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Technology	Cat5/5e; Cat6; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>