



**Catalog Number:** TY100-18-ANTI  
**Product ID:** 7TAG054970R0000  
**UPC Number:** 78621008508  
**EAN Number:** 05415022436228  
**Status:** A

Antimicrobial Treated Cable Tie, Ivory Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/2S Rated for AH-2 Plenum, Length of 104mm (4.1 Inches), Width of 2.4mm (0.095 Inch), Thickness of 1.1mm (0.045 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), Minimum Bundle Diameter 1.5mm (0.059 Inch), Maximum Bundle Diameter 22mm (0.866 Inch)

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Antimicrobial
Width	0.095 in ; 2.4 mm
Length	4.1 in ; 104 mm
Thickness	0.045 in ; 1.1 mm
Bundle Diameter	0.059 to 0.87 in ; 1.5 to 22 mm
Material	Nylon/Polyamide 6.6
Color	Ivory
Lock Mechanism	Plastic Pawl
Tensile Strength	18 pounds ; 80 newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.4mm
Length belt/tape/tie	104mm
Tie thickness	1.1mm
Max. bundle diameter	22mm
Min. holding force	80N
Operating temperature	-60-+85°C
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Other
Halogen free	Y
Colour	Cream
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	9x5x.5
Outer Quantity	10000
Outer Dimensions (inches)	11.25x7.37x10.75
Weight Uom	0.76 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001570
Marketing Brochure US	Available on Website

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)