

MB4/6.L3



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

General Information

Extended Product Type:	MB4/6.L3
Product ID:	1SNA115407R1400
EAN:	3472591154078
Catalog Description:	MB4/6.L3 Distribution Terminal Blocks
Long Description:	MB4/6.L3 Distribution Terminal Blocks - Grey,4mm ² RatedCrossSection, 2 0.5mm Spacing G32, TH 35-7.5, TH 35-15 Rail.

Ordering

Color:	grey
Minimum Order Quantity:	5 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-G Distribution terminals
Instructions and Manuals:	1SNC160001C0207-CH-G Distribution terminals

Dimensions

Product Net Width:	20.5 mm
Product Net Height:	44.5 mm
Product Net Depth / Length:	40.5 mm
Product Net Weight:	27 g

Technical

Rated Cross-Section:	4 mm ²
Spacing:	6 mm
Connection Type:	Screw clamp
Function:	Distribution
Number of Levels:	1
Rated Impulse Withstand Voltage (U_{imp}):	8 kV
Pollution Degree:	2
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	9.5 mm
Recommended Screw Driver:	4 mm

Tightening Torque: acc. IEC 60947-1 0.5 N·m
Manufacturer 0.8 N·m

Technical UL/CSA

Flammability According to UL94: V2

Environmental

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225007U1000

EAC Certificate: 1SND161009A1100

Environmental Information: 1SND220038E1002

Instructions and Manuals: 1SNC160001C0207-CH-G Distribution terminals

RoHS Information: 1SND230023F0202

Classifications

Object Classification Code: X

ETIM 4: EC001894 - Distributor assembly terminal blocks

ETIM 5: EC001894 - Distributor assembly terminal blocks

ETIM 6: EC001894 - Distributor assembly terminal blocks

Container Information

Package Level 1 Units: 5 piece

Package Level 1 Width: 50 mm

Package Level 1 Depth / Length: 133 mm

Package Level 1 Height: 49 mm

Package Level 1 Gross Weight: 0.135 kg

Package Level 1 EAN: 3472591154078

Package Level 2 Units: 150 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 500 mm

Package Level 2 Height: 150 mm

Package Level 2 Gross Weight: 4.55 kg

Package Level 3 Units: 7200 piece

Product Packing Type: Box

