

INSTRUMET 19" CASES

Home Page

E-Mail Us

Catalogue PDF

Get a Catalogue

oot a catalogu

Get a Drawing

Get a Price

Get a Quote

Customising

IP Ratings

Colour Chart

Ordering Info

7 01489 583858

📮 01489 583836

FEATURES:

- Modern aluminium 19" instrument cases
- Light weight yet robust construction
- Conforms to DIN 41494 & IEC 297-1
- Designed to accept standard 3U x 19" subracks, chassis and front panels
- Attractive design with die-cast front and rear bezels and fabricated case body
- Two versions, in three sizes
- Standard models with ABS side handles
- Portable models with tilt/swivel aluminium carry handle bar
- · Supplied fully assembled and ready to use
- Internal subrack/chassis support rails
- Removable rear panel included
- Ventilation holes in base and rear panels
- Three M4 earth studs provided inside
- Moulded ABS non-slip tilt feet included
- Anodised 10.5"/19" front panels available as accessories

MATERIAL:

• Aluminium

PROTECTION CLASS:

< IP 40 (Not rated)

STANDARD COLOUR:

- Front bezel window grey, RAL 7040
- Case body light grey, RAL 7035 (powder polyester paint)

SUPPLY:

- 1. Front/rear bezel (x2)
- 2. Top cover
- 3. Base panel
- 4. Rear panel
- 5. Chassis support
- 6. ABS Side handle
- 7. Aluminium carry handle
- 8. ABS tilt feet
- 9. M4 x 10 mm (x8)
- M4 x 12 mm (x4)
- 10. M3 x 8 mm (x12)


ACCESSORIES:

- 10.5"/19" Front Panel
- 19" Subrack/ Front Panel Mounting Kit

APPLICATIONS:

 19" subrack or chassis based electronics such as test and measurement equipment, networking and communications devices, industrial computers, sound and studio systems, laboratory instruments and industrial control systems.










ABS Tilt Feet Accessory Front Panels









For case	Part No. Aluminium Front Panel		Part No. Subrack/Front Panel Mtg Kit*	Drawings	
3U x 10.5"	M6010001	£		PDF	DWG
3U x 19"	M6019001	£		PDF	DWG
All			M6000035 £		

Notes:

- * Front Panel Kit Anodised front panel * 19" Subrack/Front Panel Mounting Kit 4 M6 caged nuts, 4 M6 Screws & 4 ABS plastic washers (RAL 7035)





Tel: (01489) 583858 Last Updated: 27-Feb-2008 ©OKW Enclosures Ltd. UK. All rights reserved.

