



**RoHS
Compliant**



Specifications

Rating Current	: 6 Amperes, 150V AC
Min. Insulation Withstand Voltage	: 2,000V AC
Insulation Resistance	: >2,000MΩ 500V DC
Operating Temperature	: -40°C to +105°C
Wire Strip Length	: 10mm
Wire Range	: 20 to 26 AWG

Diagram



Dimensions : Millimetres (Inches)

Specification Table

No.	Material	Plating / Finish	Remark	
1	Insulating Body	Polyamide 66	-	Green
2	Terminal	Brass	Tin Plated	-
3	Lever	Polyamide 66	-	Orange
4	Cover		-	Green
5	Spring	Stainless Strip Steel	-	-

Dimensions Table

Pitch : 2.54mm (0.1 inch)		
Poles	A (mm)	A (Inch)
2	8.08	0.318
3	10.62	0.418
4	13.16	0.518
5	15.7	0.618
6	18.24	0.718
8	23.32	0.918
10	28.4	1.118
12	33.48	1.318

Part Number Table

Description	Part Number
Terminal Black PCB 2.54mm Clamp 02 Way	MC000009
Terminal Black PCB 2.54mm Clamp 03 Way	MC000010
Terminal Black PCB 2.54mm Clamp 04 Way	MC000011
Terminal Black PCB 2.54mm Clamp 05 Way	MC000012
Terminal Black PCB 2.54mm Clamp 06 Way	MC000013
Terminal Black PCB 2.54mm Clamp 08 Way	MC000014
Terminal Black PCB 2.54mm Clamp 10 Way	MC000015
Terminal Black PCB 2.54mm Clamp 12 Way	MC000016

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.