

USB C Multiport Adapter - USB-C Mini Travel Dock w/ 4K HDMI or 1080p VGA - 3x USB 3.0 Hub, SD Card Reader, GbE, Audio, 100W PD - Portable Docking Station for Laptop/Tablet

Product ID: DKT30CHVAUSP



This USB-C multiport adapter turns your MacBook Pro, USB-C™ laptop, Chromebook or Android (Samsung Galaxy S8, Note 9 and above) device into a workstation, anywhere you go. A USB Type-C adapter, ideal for travel, features everything from the essential HDMI or VGA video outputs and USB ports to an SD card reader and 100W PD including PD passthrough. All through a single extended length 30 cm Thunderbolt 3 or USB-C attached host cable, providing more flexibility for harder to reach laptop and tablet connections.

Two Video Output Options with HDMI or VGA

This USB-C multiport adapter features both an HDMI and VGA port providing you with two single video output options for your boardroom presentations or your workstation setup including support for an ultra-wide monitor.

Power & Charge with 100W Power Delivery 3.0

With support for USB PD 3.0 (up to 100W), the USB Type-C multiport adapter lets you power and charge your laptop, and power your peripherals when connected to a USB-C power adapter. The USB-C hub features PD passthrough so you can use your laptop's own charger to power the hub (requires 15W) and power or charge your laptop simultaneously.

All the Essential Ports with USB

The USB-C to USB 3.0 hub gives you one USB-C port (power & data) and two USB-A ports to connect your latest and legacy USB devices.



Includes Ports to Do More with SD, Audio & Gigabit Ethernet

Access your multimedia content, audio, and network with ease. The multiport adapter provides direct access to your:

- SD, SDHC™ and SDXC™ memory cards or microSD cards via the SD card slot
- Audio content via headphones or microphone through the 3.5mm 4- position audio port
- Ethernet network via the GbE port using a hard-wired connection

DKT30CHVAUSP is backed by a StarTech.com 3-year warranty and free lifetime technical support.



Certifications, Reports and Compatibility



Applications

- Seamlessly create a familiar and productive workstation wherever you travel
- Creative professionals can use the built-in card reader to access multimedia

Features

- **8-IN-1 MULTI PURPOSE DOCK:** USB-C multiport adapter eliminates the need for multiple adapters w/ 4K30Hz HDMI or 1080p VGA, 5Gbps USB (2x USB-A, USB-C), SD slot, Gigabit Ethernet, headset/mic audio jack
- **100W POWER DELIVERY 3.0:** Use your laptop's USB-C power adapter to power the dock and provide up to 85W to power & charge your laptop, w/ 15W always reserved for the USB type-c travel dock hub
- **EXTRA LONG CABLE:** 1ft (30cm) attached cable on this usb-c mini dock for extended reach to reduce port/connector strain on 2-in-1 devices like Surface Pro 7, iPad Pro, HP Elite & laptop on riser stands
- **WIDE DEVICE COMPATIBILITY:** Compatible w/ USB-C & Thunderbolt 3 laptops, tablets, or smartphones, this portable USB-C docking station works w/ HP, Lenovo, Dell, MacBook, Chromebook & Samsung Galaxy
- **WIDE OPERATING SYSTEM COMPATIBILITY:** With automatic driver setup, this all-in-one USB-C multiport adapter supports all major operating systems, including Windows, macOS, ChromeOS, iPadOS and Android

Hardware	Warranty	3 Years
	4K Support	Yes
	Audio	Yes
	Bus Type	USB 3.1 Gen 1
	Chipset ID	VIA Labs - VL102
		VIA Labs - VL161
		VIA Labs - VL817
		Genesys Logic - GL823K
		ITE Tech - IT6564
		Realtek - RTL8153B
	Cmedia - HS100-B	
	Displays Supported	1
	Fast-Charge Port(s)	No
	Port Style	Cable Adapters
	Ports	7
Performance	Audio Specifications	3.5mm Audio
	Compatible Networks	10/100/1000 Mbps
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz (VGA)
	Maximum Cable Length	11.8 in [30 cm]
	Maximum Digital Resolutions	3840 x 2160 @30Hz, 4096 x 2160 @24hz, 3440 x 1440 @60Hz (HDMI)
	MTBF	372518 hours
	Power Reservation	15W
	Type and Rate	USB 3.1 Gen 1 - 5 Gbit/s
Connector(s)	External Ports	1 - HDMI Receptacle
		1 - VGA (15 pin, High Density D-Sub) Receptacle
		1 - RJ-45 Receptacle
		2 - USB 3.1 USB Type-A (9 pin, Gen 1, 5 Gbps) Receptacle
		1 - SD Slot Receptacle
		1 - 3.5 mm Audio Receptacle Input
		1 - 3.5 mm Audio Receptacle Output
		1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Receptacle

	Host Connectors	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Plug
Power	Power Delivery	100W
	Power Source	Not Included (not required for standard applications)
Environmental	Humidity	5%~90%
	Operating Temperature	0~45°C
	Storage Temperature	-10~82°C
Physical Characteristics	Cable Length	11.8 in [30 cm]
	Color	Black & Space Gray
	Material	Aluminum and Plastic
	Product Height	116.000
	Product Length	0.6 in [1.5 cm]
	Product Width	60.000
	Weight of Product	114.000
Packaging Information	Package Height	30.000
	Package Length	170.000
	Package Width	142.000
	Shipping (Package) Weight	0.3 lb [0.1 kg]
What's in the Box	Included in Package	1 - USB-C Docking Station 1 - Quick-Start Guide

Product appearance and specifications are subject to change without notice.