


# Wire-To-Board Connectors

## 1.25mm Receptacle Housing

**multicomp** PRO




### Specifications

Current Rating	: 1A AC/DC
Voltage Rating	: 125V AC/DC
Max. Contact Resistance	: 20mΩ
Min. Insulation Resistance	: 100MΩ
Withstanding Voltage	: 250V/minute
Temperature Range	: -40°C to +85°C

### Material

Insulator	: High temperature material
Contact Material	: Phosphor Bronze
Contact	: Tin Plated.

### Diagram



Dimensions : Millimetres

### Part Number Table

Description	A (mm)	B (mm)	Part Number
Receptacle, Free, 2 Way	4.25	1.25	MC34603
Receptacle, Free, 3 Way	5.5	2.5	MC34557
Receptacle, Free, 4 Way	6.75	3.75	MC34729
Receptacle, Free, 5 Way	8	5	MC34559
Receptacle, Free, 6 Way	9.25	6.25	MC34351
Receptacle, Free, 7 Way	10.5	7.5	MC34561
Receptacle, Free, 8 Way	11.75	8.75	MC34353
Receptacle, Free, 9 Way	13	10	MC34563
Receptacle, Free, 10 Way	14.25	11.25	MC34731
Receptacle, Free, 11 Way	15.5	12.5	MC34565
Receptacle, Free, 12 Way	16.75	13.75	MC34457
Receptacle, Free, 13 Way	18	15	MC34567
Receptacle, Free, 14 Way	19.25	16.25	MC34569
Receptacle, Free, 15 Way	20.5	17.5	MC34325

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro

**multicomp** PRO