



## CREAM SYNTHETIC GLOVES POWDER FREE

CODE: SWF2701/02/03/04

- Examination gloves - regular duty
- Beaded Cuff - providing additional strength and preventing liquid roll off
- Latex Free - to reduce the risk of hypersensitivity and allergic reactions
- Special formulation for maximum strength and increased resistance
- DOP and EHP free
- Ambidextrous
- Powder Free

### Suitable for use in:

- Janitorial
- Automotive
- Healthcare
- Laboratory

**1FirstHand**  
HYGIENE DISPENSE SYSTEM

**UNIQUE SINGLE  
HYGIENE DISPENSE  
GLOVE SYSTEM**  
REDUCING THE RISK OF  
CROSS CONTAMINATION



TECHNICAL DATA ON REVERSE ▲

**HAZEL 4D**

Mill House, Troy Road  
Horsforth, Leeds, LS18 5TN

[wecare@hazel4d.com](mailto:wecare@hazel4d.com)



# CREAM SYNTHETIC GLOVES POWDER FREE

CODE: SWF2701/02/03/04

## DIMENSIONS

| Size Palm Width (mm) | Palm Width (mm) | MGM Length (mm) | ASTM D3578-05 Length (mm) |
|----------------------|-----------------|-----------------|---------------------------|
| S                    | 80              | Min. 240        | Min. 230                  |
| M                    | 95              | Min. 240        | Min. 230                  |
| L                    | 105             | Min. 240        | Min. 230                  |
| XL                   | 113             | Min. 240        | Min. 230                  |

## THICKNESS

| Location of Thickness Measurement | Single Wall (mm) |
|-----------------------------------|------------------|
| Finger                            | Min. 0.18        |
| Palm                              | Min. 0.09        |
| Cuff                              | Min. 0.07        |

## TEST RESULT

|                     | Inspection Level | AQL |
|---------------------|------------------|-----|
| Watertight Test     | G1               | 1.5 |
| Watertight Test     | G1               | 1.5 |
| Minor Defects       | G1               | 1.5 |
| Dimensions          | S2               | 1.5 |
| Physical Properties | S2               | 1.5 |

## PHYSICAL PROPERTIES

|                  | Before Aging | After Aging |
|------------------|--------------|-------------|
| Tensile Strength | Min. 13      | Min. 11     |
| Elongation (%)   | Min. 350     | Min. 300    |

## MATERIAL SAFETY DATA:

Constructed from a hybrid mixture of PVC (Poly Vinyl Chloride and Synthetic NBR (Nitrile Butadiene Rubber)

Non-Sterile

Store in a cool dry area away from sunlight

Disposal: Landfill or incineration

Stop use immediately if rashes or other signs of skin irritation appear.

## ORDERING INFORMATION

| Code    | Description                          | Size/Colour | Quantity per inner | Quantity per Carton | Inners per Carton |
|---------|--------------------------------------|-------------|--------------------|---------------------|-------------------|
| SWF2701 | Cream Synthetic Gloves - Powder Free | Small       | 100                | 1000                | 10                |
| SWF2702 | Cream Synthetic Gloves - Powder Free | Medium      | 100                | 1000                | 10                |
| SWF2703 | Cream Synthetic Gloves - Powder Free | Large       | 100                | 1000                | 10                |
| SWF2704 | Cream Synthetic Gloves - Powder Free | X-Large     | 100                | 1000                | 10                |

## SYMBOLS



## APPROVED BY



## IN ACCORDANCE WITH

- Medical Device Directive - 93/42/EEC Class 1 (2007/47/EC)
- EN455-1,2,3,4 - Medical Gloves for Single use.
- Manufactured under ISO 9001:2008 and 13485:2012

**Hazel 4D**  
Mill House  
Troy Lane  
Horsforth  
Leeds  
LS18 5TN