

# 1/4" + 1/2" Tool Set with 110 Tools

## CTK110EU

# Crescent®

Case with practical carrying handle and integrated tool mounting plates

40 Screwdriver Bits

1 Magnetic Bit Driver

5 different extensions

2 Quick Release Ratcheting Drive with 72-tooth and ergonomic cushion grip

2 Spark Plug Socket with

15 Sockets in Chrome-Vanadium and SuperLock



## Contents

Sockets matte chromed  
Pliers chrome/nickel, mirror finish, with cushion grip

- 1 1/2" Quick Release Ratcheting Drive, 72-tooth, with cushion grip, CrV
- 1 1/2" Extension 125 mm, CrV
- 1 1/2" Universal Joint, CrV
- 15 1/2" Sockets 10 / 11 / 12 / 13 / 14 / 15 / 17 / 18 / 19 / 20 / 21 / 22 / 23 / 24 / 27 mm, CrV, 6 pt
- 1 1/2" Sliding T-Handle / Extension 250 mm, CrV
- 1 1/2" Spark Plug Socket 16 mm, CrV
- 1 1/2" Spark Plug Socket 21 mm, CrV
- 1 1/4" Quick Release Ratcheting Drive, 72-tooth, with cushion grip, CrV
- 2 1/4" Extension 50 mm and 100 mm, CrV
- 1 1/4" Universal Joint, CrV
- 1 1/4" Flexible Extension 150 mm, CrV
- 11 1/4" Sockets 4 / 5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, CrV, 6 pt
- 11 Combination Wrenches 8 / 9 / 10 / 11 / 12 / 13 / 14 / 15 / 17 / 18 / 19 mm, CrV
- 2 Screwdriver, Slotted 6,5 x 100 mm and 5,5 x 75 mm
- 2 Screwdriver, Phillips® No. 1 x 75 mm and No. 2 x 100 mm
- 1 Magnetic Bit Driver, 125 mm, CrV
- 40 Screwdriver Bits 1/4", 25 mm long
- 4 Bit Holders
- 8 Hex Keys 1,5 / 2 / 2,5 / 3 / 4 / 5 / 5,5 / 6 mm
- 1 Hex Key Holder
- 1 Long Nose Plier w/Spring 8", 200 mm, CrNi
- 1 Diagonal Cutting Plier w/spring 6", 150 mm, CrNi
- 1 Tongue & Groove Plier 7", 175 mm, CrNi

Case with blister inlay and 4c coloured display box  
Weight: 8,3 kg  
Sizes: 515 mm x 920 mm x 52 mm

The Set includes 110 pieces in high-quality Chrome-Vanadium (except pliers). All pieces are fixed in a handy plastic case.

Order No.: CTK110EU

