

Product Specification

Guideway



Exit Sign Recessed
 EGR1LS1LTC-S22



Exit Sign Suspended
 EGR1LS1LTC-S22 + EG-WKIT150

EGR1LS1LTC-S22

REC LED SIGN SLAVE LTC 230VAC 22M

Catalogue Number	EGR1LS1LTC-S22
Category	Sign luminaire
GTIN	05415022444711
GID	7TCA091140R0530
Warranty (Year)	5
Other	Refer to ABB warranty terms & conditions

Power Supply System	Mains / Slave Operation
Mounting Method	Ceiling, Wall
Mounting Form	Recessed
Material Housing	Aluminium/Plastic
Colour Housing	Aluminium
Material Cover	No cover supplied
Material	Aluminium/ Polycarbonate
Colour	Aluminium
Length (mm)	235
Width (mm)	84
Height/depth (mm)	134
Nominal Voltage (V)	220-240
Voltage Type	AC 50/60Hz
Duration (hours)	Mains / Central Battery
Battery	Mains / Central Battery
Monitoring Equipment	EMEX test
Lamp Type	LED
Lamp Power	2
Number of Lamps	1
Light output in Emergency Operation (lm)	Not Applicable
Average Lifespan light source (hours)	100000
Colour of Light	White
Colour Temperature (K)	5000
CRI	80
Degree of Protection (IP)	40
Impact Strength (IK)	
Wiring System	Maintained / non-maintained circuit
Type of Legend	Single or Double Sided

Legend style	Insert sheet/plate
Recognition distance (m)	22
Power Consumption Maintained mode (W)	4
Power Consumption Maintained mode (VA)	4.4
Nominal current (mA)	19
Inrush Current (A to 0.1ms)	
Power Factor	0.9
Temperature range (°C)	0 to 35°C
Weight (Kg)	1.2
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	300 x 205 x 88

Accessories

XEN2EG22 Down ISO7010 Legend Single Sided

XEN3EG22 Left ISO7010 Legend Single Sided

XEN6EG22 Right ISO7010 Legend Single Sided

XEN5EG22 Up ISO7010 Legend Single Sided

XBN1EG22 Arabic English Legend Single Sided

XEN0G22 Blank Legend Single Sided

XEN602EG22 Down ISO7010 Legend Flag Mount

XEN603EG22 Left ISO7010 Legend Flag Mount

XEN606EG22 Right ISO7010 Legend Flag Mount

XEN605EG22 Up ISO7010 Legend Flag Mount

EG-T4SG Cover Discs (2x semi-circular, 2x rectangular) for Self-Contained

EG-T4EG Cover Discs (2x semi-circular, 2x rectangular) for Slave

EG-TKIT50 Suspension Kit Pendant 50mm

EG-TKIT100 Suspension Kit Pendant 100mm

EG-WKIT150 Wire Suspension Kit 150mm