

WALL SENSE WALL CIRCLE SENSE 0053642



Product features

- Battery operated portable light designed for various lighting applications where no suitable electrical socket is available. Uniform light output. Attractive and functional design. Integrated motion and day/night sensor. Low power consumption. IP44 - suitable for roofed outdoor areas. Versatile can be used for a wide range of indoor and outdoor applications like entrance lighting, corridors, balconies, patios, garage. Auto / On / Off switch. 3xAA batteries included.



PRODUCT OVERVIEW

IPC Code	0053642
Product name	WALL CIRCLE SENSE
Technology	LED
General application	Residential & Consumer
Certifications	EUNEW009
ETIM Class	EC000987
E-number FI	8709902
Fixture luminous flux (lm)	40
Luminaire efficacy (lm/W)	26
Colour temperature (K)	4000
CRI (Ra)	80
Photobiological Risk Group	RG0
Total power consumption (W)	1.5
Electrical protection	Class III
IP rating	IP44
IK rating	IK02
Product EAN number	5410288536422
Lamps	Yes
Included lamp	INTEGRATED LED

DATA TABLE

General data

IPC Code	0053642
Product name	WALL CIRCLE SENSE
Technology	LED
General application	Residential & Consumer
Certifications	EUNEW009
ETIM Class	EC000987
E-number FI	8709902

Optical data

Fixture luminous flux (lm)	40
Luminaire efficacy (lm/W)	26

WALL SENSE WALL CIRCLE SENSE 0053642

Colour temperature (K)	4000
CRI (Ra)	80
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	1.5
Mains voltage (V)	4.5V
Electrical protection	Class III
Drive current (mA)	225

Lifetime data

Lumen maintenance - L70 B50	15000
-----------------------------	-------

Physical data

IP rating	IP44
IK rating	IK02
Nominal Product Length (mm)	110
Nominal Product Width (mm)	110
Nominal Product Height (mm)	56
Weight (kg)	0.215


Packaging

Single packaging type	Carton
Product EAN number	5410288536422
Packaging single length / height (cm)	21.5
Packaging single width (cm)	20.0
Packaging single depth (cm)	6.5
DUN14 (outer)	15410288536429
Units per outer package	6
Packaging outer length / height (cm)	24.0
Packaging outer width (cm)	23.0
Packaging outer depth (cm)	40.0

Safety data


Safety message	Not Suitable for totally enclosed fixtures
----------------	--------------------------------------------


TECHNICAL DRAWINGS




WALL SENSE WALL CIRCLE SENSE 0053642


SYLVANIA 0053642


 This luminaire contains built-in LED lamps




The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built-in LED lamps



The lamps cannot be changed in the luminaire.

SYLVANIA 0053642 

874/2012