

[PRODUCTS FOR BUSINESS](#) ▼[PRODUCTS FOR CONSUMERS](#) ▷[ABOUT US](#) ▷[SCIENCE CENTRE](#) ▷[Products](#) > [Personal Protective Equipment](#) > [Ear plugs & Earmuffs](#) > [Peltor](#) > [Communications Solutions](#) > [Headsets](#) > 3M™ PELTOR™

3M™ PELTOR™ LiteCom FRS Headset MT53H7A4602-NA, Headband, NRR 25, CSA Class A

3M ID 7100204442


Overview

Details

Specifications

Featured content

Contact a representative



- Helps provide hearing protection when exposed to hazardous noise
- Uses an analog two-way communication radio with 22 pre-programmed FRS/GMRS channels
- Noise-canceling microphone for clear speech transmission in noisy environments

[View Images](#)

- Push-to-Talk (PTT)
or hands-free Voice
Operated (VOX)
transmit options

[View all details](#)

Details

The 3M™ PELTOR™ LiteCom FRS Headset is a versatile hearing protector with a built-in analog two-way radio. Programmed to operate on the 22 FRS/GMRS channels, this headset comes equipped with a noise-canceling, voice-operated speech microphone that helps enable clear, hands-free communication in noisy environments. Keep connected and stay informed with the 3M™ PELTOR™ LiteCom FRS Headset.

Each setting and control on the 3M™ PELTOR™ LiteCom FRS Headset is designed to be intuitively simple. To activate the noise-canceling microphone, simply press the Push-to-Talk (PTT) button on the earcup or by using the voice-operated transmission (VOX). As the wearer speaks into the microphone, the channel is opened in milliseconds, allowing for clear, near-instantaneous communication. This functionality, combined with the professional-grade durability and wearability synonymous with 3M™ PELTOR™ Brand products, makes the 3M™ PELTOR™ LiteCom FRS Headset an ideal protection solution.

- Helps provide hearing protection when exposed to hazardous noise
- Uses an analog two-way communication radio with 22 pre-programmed FRS/GMRS channels
- Noise-canceling microphone for clear speech transmission in noisy environments
- Push-to-Talk (PTT) or hands-free Voice Operated (VOX) transmit options
- Voice-guided headset menu for easy operation
- Built tough for the working professional while offering comfortable all-day wearability

- Comes equipped with two AA batteries

Suggested Applications

- Designed for use in noisy working environments
- An ideal choice for jobs like construction, manufacturing, processing, equipment maintenance, crane operations, and plant tours

Specifications

Attenuation	25 dB
Battery Life	Approx. 20 hours
Battery Type	AA or Rechargeable NiMH Pack
Brand	PELTOR™
Communication Type	Two-way radio
Connection Type	J22 Audio Input
CSA Class	CSA Class B
Features	Built in communication radio, Two Way Communication
Hearing Protection Style	Earmuffs
Hearing Protection Type	Neckband
Intrinsically Safe	No
Microphone Class/Type	Electret
Net Weight (Metric)	394 g

Product Colour	Dark Blue
-----------------------	------------------

Product Series	Lite-Com
-----------------------	-----------------

Product Type	Protective Communication
---------------------	---------------------------------

Recommended Application	Construction, Facility Maintenance, High Noise Environment, Machine Operations, Manufacturing
--------------------------------	--

Recommended Industry	Agriculture, Construction, Forestry, Manufacturing, Mining
-----------------------------	---

Standards/Approvals	CSA, FCC/ISED
----------------------------	----------------------

Featured content



Have you heard?

Sound solutions.

Applied to hearing loss prevention.

From half time to hammer time.
From weekends downtown to working underground.
From Friday night to the job site.
Hearing loss can be caused by a one-time exposure to an intense impulse sound. Discover

The Damaged Hearing Experience

With hearing damage, what else could you experience?
Discover how 3M science helps you get smarter about hearing protection.
<http://s.3m.com/Zac96m>

Contact a representative

Need help choosing the right personal protective equipment for your application? We'd be happy to help.

All fields are required unless indicated optional.

Personal information

First name**Last name****Email****Phone number**

Enter your 10-digit phone number. Numbers only (5555555555).

Job title**Company****Number of employees wearing personal protective equipment (PPE)**

- ☐ 1 - 10
- ☐ 11 - 70
- ☐ 71 - 150
- ☐ More than 150

Mailing information

Address

Message — *Optional*

Please provide any additional information you believe would allow us to serve you better.

3M will use the information to respond to your request and in accordance with our [Privacy Policy](#).

☐ **Opt-in:** I would like to receive electronic messages, which may include promotions, product information and service offers, from 3M. I understand that I may unsubscribe at any time using the opt-out link provided in every electronic message.

3M takes your privacy seriously. 3M and its authorized third parties will use the information you provided in accordance with our [Privacy Policy](#) to send you communications, which may include promotions, product information and service offers.

Contact us