

MASTER TL5 High Output

MASTER TL5 HO 24W/830 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Product data

General Information		
Cap-Base	G5 [G5]	
Life to 50% Failures Preheat (Nom)	30000 h	
Features	na [Not Applicable]	
System Description	High Output	
LSF Preheat 2000 h Rated	99 %	
LSF Preheat 4000 h Rated	99 %	
LSF Preheat 6000 h Rated	99 %	
LSF Preheat 8000 h Rated	99 %	
LSF Preheat 16000 h Rated	97 %	
LSF Preheat 20000 h Rated	84 %	
Color Rendering Index (Max)		85
Color Rendering Index (Min)		80
Color Rendering Index (Nom)		82
LLMF 2000 h Rated		96 %
LLMF 4000 h Rated		95 %
LLMF 6000 h Rated		94 %
LLMF 8000 h Rated		93 %
LLMF 12000 h Rated		92 %
LLMF 16000 h Rated		91 %
LLMF 20000 h Rated		90 %
Light Technical		
Color Code	830 [CCT of 3000K]	
Luminous Flux (Nom)	1950 lm	
Luminous Flux (Rated) (Nom)	1700 lm	
Color Designation	Warm White (WW)	
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	87 lm/W	
Correlated Color Temperature (Nom)	3000 K	
Luminous Efficacy (rated) (Nom)	76 lm/W	
Operating and Electrical		
Power (Nom)	22.5 W	
Lamp Current (Nom)	0.295 A	
Temperature		
Design Temperature (Nom)	35 °C	

MASTER TL5 High Output

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	Green Plate
----------------------	-------------

Approval and Application


Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	25 kWh

Product Data

Full product code	871150063958555
-------------------	-----------------

Order product name	MASTER TL5 HO 24W/830 SLV/40
EAN/UPC - Product	8711500639585
Order code	927928083055
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927928083055
Net Weight (Piece)	52.000 g
ILCOS Code	FDH-24/30/1B-L/P-G5-16/550

Dimensional drawing




Product


MASTER TL5 HO 24W/830 SLV/40

TL5 HO 24W/830

Photometric data





LDPB_TL5-HO8_830-Spectral power distribution B/W



LDPO_TL5-HO8_830-Spectral power distribution Colour


MASTER TL5 High Output

Lifetime



LDLE_TL5-HO8_0001-Life expectancy diagram

LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

