

MASTER TL5 High Output

MASTER TL5 HO 39W/840 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	na [Not Applicable]
System Description	High Output
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux (Nom)	3500 lm
Luminous Flux (Rated) (Nom)	3100 lm
Color Designation	Cool White (CW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	92 lm/W
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	82 lm/W

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Nom)	38.0 W
Lamp Current (Nom)	0.325 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

MASTER TL5 High Output

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	Green Plate
----------------------	-------------

Approval and Application


Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	42 kWh

Product Data

Full product code	871150063964655
-------------------	-----------------

Order product name	MASTER TL5 HO 39W/840 SLV/40
EAN/UPC - Product	8711500639646
Order code	927928584055
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927928584055
Net Weight (Piece)	79.200 g
ILCOS Code	FDH-39/40/1B-L/P-G5-16/850

Dimensional drawing




Product


MASTER TL5 HO 39W/840 SLV/40

TL5 HO 39W/840

Photometric data




LDPB_TL5-HO8_840-Spectral power distribution B/W



LDPO_TL5-HO8_840-Spectral power distribution Colour


MASTER TL5 High Output

Lifetime



LDLE_TL5-HO8_0001-Life expectancy diagram

LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

