




Acer recommends Windows 10 Pro for business.



TravelMate P2



Camera shutter



MIL-STD 810G
Compliant



HDD+SSD



Face Login



Fingerprint Reader
& Windows Hello



Reversible type-C
connector

4GLTE

Internet
Connection



Type-C Dock
compatible





Wi-Fi 6

SPECIFICATIONS

TravelMate P2

TMP215-52 / TMP215-52G



Product views	1. Microphones 2. Webcam shutter 3. Webcam 4. 15.6" display 5. DC-in jack 6. RJ-45 port 7. VGA port	8. HDMI® port 9. USB 3.1 Gen 1 port with power-off charging 10. USB 3.1 port 11. USB Type-C port with DC-in 12. SD card reader 13. Headset/speaker jack	14. Fingerprint reader(optional) 15. Touchpad 16. Smart Card reader(optional) 17. Power button 18. Keyboard 19. NFC transmitter(optional)	20. Power indicator 21. Battery indicator 22. USB 3.1 port 23. SIM card slot(optional) 24. Kensington lock slot 25. Speakers
Operating system ^{1,2}	Windows 10 Pro 64-bit (Acer recommends Windows 10 Pro for business.) Windows 10 Home 64-bit			
CPU and chipset ¹	Intel® Core™ i7-10510U processor	Intel® Core™ i5-10210U processor	Intel® Core™ i3-10110U processor	
Memory ^{1,3,4,5}	Dual-channel DDR4 SDRAM support ● Up to 16 GB of DDR4 system memory, upgradable to 32 GB using two soDIMM modules			
Display ⁶	15.6" display with IPS (In-Plane Switching) technology, Full HD 1920 x 1080, Acer ComfyView™ LED-backlit TFT LCD ● 16:9 aspect ratio ● Wide viewing angle up to 170 degrees ● Ultra-slim design ● Mercury free, environment friendly	15.6" Full HD 1920 x 1080, high-brightness Acer ComfyView™ LED-backlit TFT LCD ● 16:9 aspect ratio ● Ultra-slim design ● Mercury free, environment friendly	15.6" HD 1366 x 768 resolution, high-brightness Acer ComfyView™ LED-backlit TFT LCD ● 16:9 aspect ratio ● Ultra-slim design ● Mercury free, environment friendly	
Graphics ⁷	Intel® UHD Graphics	NVIDIA® GeForce® MX230 (TMP215-52G only)		
Audio	● Two built-in stereo speakers		● Built-in digital microphone	
Storage ^{1,8}	Solid state drive ● 512 GB / 256 GB, PCIe Gen3, 8 Gb/s up to 4 lanes, NVMe ● 128 GB, PCIe Gen3, 8 Gb/s, NVMe		Hard disk drive ● 1 TB 2.5-inch 7200 RPM ● 1 TB / 500 GB 2.5-inch 5400 RPM	
Webcam ¹	HD camera with 1280 x 720 resolution and 720p HD audio/video recording			
Wireless and networking ¹	WLAN ● Intel® Wireless Wi-Fi 6 AX201 ● 802.11a/b/g/n/ac/ax2+ax wireless LAN ● Dual Band (2.4 GHz and 5 GHz) ● 2x2 MU-MIMO technology ● Supports Bluetooth® 5.0 ● Wi-Fi CNVi Interface	LAN ● Gigabit Ethernet, Wake-on-LAN ready WWAN ● LTE FDD: B1/B3/B5/B7/B8/B20/B28/B32 ● LTE TDD: B38/B40/B41 ● WCDMA/HSPA+: B1/B2/B5/B8 ● Support up to LTE Cat.6 ● LTE FDD: Maximum download 300 Mbps, upload 50 Mbps.	● LTE TDD: Maximum download 226 Mbps, upload 28 Mbps. ● UMTS: Maximum download 384 Kbps, upload 384 Kbps ● HSUPA: Maximum download 5.76 Mbps ● DC-HSPA+: Maximum download 42 Mbps ● Support Text Message (SMS) ● eSIM (selected models)	
Security	Acer ProShield Security Manager including: ● Data Protection: File Encryption & Decryption, Personal Secure Drive ● Data Removal: File Shredder		Discrete Trusted Platform Module (TPM) solution BIOS user, supervisor passwords, Kensington lock slot	
Dimensions and weight ^{1,9,10}	Dimensions: 363 (W) x 255 (D) x 19.9 (H) mm (14.29 x 10.04 x 0.78 inches)		Weight: 1.8 kg (3.97 lbs.) with 3-cell battery pack, one SSD	
Power adapter and battery ^{1,11}	Power adapter ● 3-pin 45 W AC adapter (TMP215-52 only) ● 3-pin 65 W AC adapter (TMP215-52G only)		Battery ● 48 Wh 3-cell Li-ion battery (for models with Full HD Panel + SSD) ● Battery life up to 15 hours (based on web browsing test results) (TMP215-52 only) ● Battery life up to 14 hours (based on web browsing test results) (TMP215-52G only)	
Input and control	Keyboard 87-/88-/91-key Acer FineTip backlit keyboard with Home, End, Pg Up, Pg Dn keys, international language support, power button 87-/88-/91-key FineTip keyboard with Home, End, Pg Up, Pg Dn keys, international language support, power button Touchpad Multi-gesture secure touchpad, supporting two-finger scroll; pinch; gestures to open Cortana, Action Center, multitasking; Fingerprint application commands ● Windows Hello Certification ● Microsoft Precision Touchpad certification Multi-gesture touchpad, supporting two-finger scroll; pinch; gestures to open Cortana, Action Center, multitasking; application commands ● Microsoft Precision Touchpad certification ● Moisture resistant			
Windows Desktop Apps ¹²	● Acer Collection ● Quick Access	● Acer Control Center ● Acer Product Registration	● Acer Proshield	
System compliance ¹³	● ENERGY STAR®		● Wi-Fi®	● EPEAT® registered
Warranty	One-year International Travelers Warranty (ITW)			

Acer recommends Windows 10 Pro for business.

- Specifications vary depending on model.
- 64-bit software is required to enjoy the advantages of 64-bit processing.
- Shared system memory may be allocated to support graphics, depending on system memory size and other factors. Actual system memory available to the operating system will be reduced by any memory used by the graphics solution and resources required by the operating environment.
- Memory speed may vary, depending on the CPU, chipset or memory fitted.
- A 64-bit operating system is required to enjoy the ultimate performance of 4 GB or higher memory.
- All brands and product names mentioned herein include trademarks of their respective companies and are used solely to describe or identify the products.
- Not all features indicated are supported on all SKUs
- 1 GB is 1 billion bytes, 1 TB is 1000 GB. Actual formatted capacity is less and may vary depending on preloaded materials and operating environment. Acer Recovery Management uses a portion of the stated hard disk capacity as dedicated backup space.
- Minor variations in system dimensions are possible due to the manufacturing process.
- Weight may vary depending on product configuration, vendor components, manufacturing variability, and selected options.
- Listed battery life is based on testing using Web browsing. The test clip loops the loading of 50 selected websites using Microsoft Edge every 30 seconds, until the battery is drained. Stated battery life is for comparison purpose only. Actual battery life varies by model, configuration, applications, video chip format and features used. A battery's maximum capacity decreases with time and use. Battery life test configuration: 10th Gen Intel® Core™ i5, FHD, SSD only, 8GB of DDR4 memory. Battery life test condition: 100 nits LCD brightness, 50% speaker volume, WLAN on, Bluetooth on, no WW direct Internet connection.
- Bundled software may vary depending on hardware configuration, OS and regional availability.
- EPEAT® registration varies by country. See <http://www.epeat.net/> for registration status for each country.

In a continuing effort to improve the quality of our products, information in this document is subject to change without notice. Images shown are only representations of some of the configurations available for this model. Availability may vary depending on region.

As a phenomenon known to thin-film transistors (TFTs), liquid crystal displays (LCDs) commonly exhibit a small number of discoloration dots, as so-called "non-conforming pixels." This phenomenon is a limitation of TFT LCD technology, not a product defect, and as such is not covered by Acer's warranty.

© 2019. All rights reserved.

Microsoft and Windows are registered trademarks of Microsoft Corporation.

Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi, Xeon Inside, and Intel Optane are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries.

About Acer

Founded in 1976, Acer is now one of the world's top ICT companies and has a presence in over 160 countries. As Acer looks into the future, it is focused on enabling a world where hardware, software and services will fuse with one another to open up new possibilities for consumers and businesses alike. From service-oriented technologies to the Internet of Things to gaming and virtual reality, Acer's 7,000+ employees are dedicated to the research, design, marketing, sale, and support of products and solutions that break barriers between people and technology. Please visit www.acer.com for more information.