

2 Port USB C KVM Switch - 4K 60Hz HDMI - Compact Dual Port UHD USB Type C Desktop Mini KVM Switch with USB C Cables - Bus Powered - MacBook iPad Pro ThinkPad IdeaPad EliteBook
Product ID: SV211HDUC



This 2-port USB-C KVM enables you to easily switch between two USB Type-C or Thunderbolt 3 desktop or laptop computers, using a single keyboard, HDMI monitor and mouse.

Utilizing USB-C with DP alt-mode, this compact KVM switch only requires a single cable be connected to each of your computers, ensuring a small footprint with limited cabling requirements. All required cables for connecting your computers are included, to ensure a hassle-free setup right out of the box.

For easy operation, the KVM features a single button that toggles between connected computers.

The USB-C KVM switch supports UHD resolutions up to 4K (3840x2160) at 60Hz and can drive one large HDMI 2.0 display with ease, maximizing viewing space.

Along with the USB-C design that ensures cabling requires are minimum the KVM is bus powered further reducing clutter by avoiding the need for a bulky power adapter. The lightweight small form factor makes this mini KVM switch easy to deploy and is ideal for mobile/hot desk workforces.

The KVM is OS independent supporting all operating systems including Windows, Linux, macOS, iPadOS (Apple iPad Pro) and Android. StarTech.com has rigorously tested this product to ensure compatibility with all popular device brands including: Dell, HP, Apple and Lenovo.

The SV211HDUC is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- High resolution medical imaging
- Digital signage server control
- Mobile and hot-desk work forces

Features

- **SPACE-SAVING:** Compact USB C KVM switch enables easy switching between 2 USB Type C or Thunderbolt 3 desktops/laptops using 1 keyboard, monitor & mouse; OS independent and works with the Apple iPad Pro
- **2 PORT USB-C KVM:** 4K 60Hz UHD 3840x2160 HDMI 2.0 Out Push-Button Switching Bus Powered OS Independent Works with Thunderbolt 3 ports Cables included
- **PORTABLE:** USB powered feature reduces clutter by avoiding the need for power adapter while the lightweight small form factor makes the mini KVM Switch easy to carry for the mobile/ hot desk workforce
- **READY TO USE:** USB-C cables for host computers are included w/ the dual port KVM switch, providing easy to deploy solution straight out of the box; works w/popular brands like Dell, HP, Apple & Lenovo
- **THE STARTECH.COM ADVANTAGE:** StarTech.com offers a 2-year warranty and free lifetime 24/5 multilingual technical support based in North America on this 2 port KVM switch

Hardware	Warranty	2 Years
	Audio	Yes
	KVM Ports	2
	PC Interface	USB-C
	PC Video Type	USB-C (DP Alt-Mode)
	Number of Monitors Supported	1
	Rack-Mountable	No
	Cables Included	Yes
	Chipset ID	Parade - PS176
	Chipset ID	VLI - VL170
	Chipset ID	Terminus - FE1.1S
	Chipset ID	No
	Daisy-Chain	No
Performance	On-Screen Display	No
	Video Revision	DisplayPort 1.2
	Video Revision	HDMI 2.0
	IP Control	No
	Hot-Key Selection	No
	Maximum Data Transfer Rate	480Mbps
	Yes	

Wide Screen Supported	
Audio Specifications	HDMI - 7.1 Channel Audio
Port Selection Support	Push Button
MTBF	50,000 hours

Connector(s)	Console Interface(s)	USB Type-A (4 pin) USB 2.0
	Console Interface(s)	HDMI (19 pin)
	Host Connectors	USB Type-C (24-pin) USB 2.0 (480Mbps)

Special Notes / Requirements	System and Cable Requirements	Your USB-C ports must support DisplayPort over USB-C (DP Alt mode) in order to work with this KVM switch
-------------------------------------	-------------------------------	--

Indicators	LED Indicators	Functional Display
	LED Indicators	Port selection or active host

Power	Power Source	Bus Powered
--------------	--------------	-------------

Environmental	Operating Temperature	5C ~ 35C
	Storage Temperature	-20C ~ 50C
	Humidity	20%RH ~ 80%RH

Physical Characteristics	Color	Black
	Material	Plastic
	Product Length	2.8 in [72.000 mm]
	Product Width	5.5 in [1.4 cm]
	Product Height	0.6 in [15.700 mm]
	Weight of Product	9.4 oz [265.000 g]

Packaging Information	Package Length	4.7 in [1.2 cm]
	Package Width	6.8 in [1.7 cm]
	Package Height	3.3 in [85.000 mm]
	Shipping (Package) Weight	19.9 oz [565.000 g]

What's in the Box	Included in Package	KVM Switch
	Included in Package	3.3 ft. [1 m] USB-C Cables



Included in Package

Quick-Start Guide

**Product appearance and specifications are subject to change without notice.*

