

Thunderbolt 3 Mini Dock - Portable Dual Monitor TB3 Docking Station with HDMI 4K 60Hz - 2x USB-A Hub (3.2/2.0) & GbE - 11" Attached Cable - TB3 Laptop Multiport Adapter - Mac/Windows
Product ID: TB3DKM2HDL



This certified Thunderbolt 3 docking station is a compact mini dock, delivering essential connections for productivity. The bus-powered dock connects dual 4K HDMI displays, Gigabit Ethernet, and two USB-A (USB 3.2 / 2.0) ports and for flexible set up, the attached Thunderbolt 3 cable has an extended length of (11 in./ 28 cm).

Great for editing 4K video or other Ultra HD tasks, this portable Thunderbolt 3 to HDMI dock supports 40 Gbps of throughput and 4K resolution at 60Hz on dual HDMI monitors, through a single Thunderbolt 3 port. Run resource-demanding applications on two independent displays without draining system resources.

- 2x 4K HDMI displays (up to 4096 x 2160p @ 60Hz)

At just 2.4" x 4.9" (6.1 cm x 12.4 cm), this dock takes up minimal room on your desk and in your laptop case. The dock's 28 cm (11 inches) attached cable provides extended reach to reduce port/connector strain on MacBooks and laptops on riser stands, or if needed, offers the flexibility to position dock further away from the laptop on your desk.


- 1x USB 3.2 Gen 1 Type-A port (5Gbps)
- 1x USB 2.0 Type-A port
- 1x Gigabit Ethernet port (with PXE Boot and Wake-on-LAN support)

As many high powered, later generation laptops optimally require more than 100W of power to stay charged, some users prefer to use their laptop's power adapter vs. using their docking stations to keep laptops charged.

This bus-powered TB3 mini dock is ideally suited for those users, providing full Thunderbolt 3 docking station performance and functionality, while their workstation laptops are separately charged.

The TB3DKM2HDL is Thunderbolt Certified and backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

Features

- **THUNDERBOLT 3 CERTIFIED MINI DOCK:** 40 Gbps video & data throughput, dual monitor 4K 60Hz HDMI output, 2-Port USB-A Hub (1x USB 3.1 Gen 1 5Gbps & 1x USB 2.0) & Gigabit Ethernet port w/ PXE boot and WoL
- **EXTRA LONG 11 INCH ATTACHED CABLE:** This Thunderbolt 3 docking station's 11in (28cm) attached cable provides extended reach to reduce port/connector strain on MacBooks and laptops on riser stands
- **COMPACT SIZE:** This bus-powered, portable thunderbolt 3 mini dock is designed for shared and small workspaces; Use this Thunderbolt 3 multiport adapter for work from home or on-the-go/travel use
- **BROAD LAPTOP COMPATIBILITY:** No driver setup; This universal TB3 dock is compatible w/ MacBook Pro 13, 16 and Air, plus Windows-based Thunderbolt 3 laptops like Dell XPS, HP EliteBook, Lenovo X1 Carbon
- **FOR HIGH POWERED LAPTOPS:** For users who need to use their laptop power adapter as they require 100W or more to keep their laptop charged; but still want Thunderbolt 3 dock performance & functionality

Hardware	Warranty	3 Years
	4K Support	Yes
	Fast-Charge Port(s)	No
	Displays Supported	2
	Audio	No
	Interface	Thunderbolt 3
	Bus Type	Thunderbolt 3
	Industry Standards	1Gb connectivity to any 1000Base-T device (IEEE802.3ab Compliant)
	Industry Standards	100Mb connectivity to any 100Base-TX device (IEEE802.3u Compliant)
	Industry Standards	10Mb connectivity to any 10Base-T device (IEEE802.3i Compliant)
	Chipset ID	Intel JHL6540 (Alpine Ridge)
	Chipset ID	Texas Instruments TPS65983A
	Chipset ID	Parade PS176
	Chipset ID	ASMedia ASM1042A
	Chipset ID	Intel WGI210

Performance	Maximum Cable Length	11.0 in [2.8 cm]
	Maximum Digital Resolutions	4K 60Hz
	PXE	Yes
Software	OS Compatibility	Windows®; 10 (32/64 bit), 8.1 (32/64bit), 7 (32/64bit) Windows®; Server 2008 R2, 2012(32/64bit) Mac OS 10.10-10.15
Power	Power Source	Bus Powered
Environmental	Operating Temperature	5C to 40C
	Storage Temperature	-20C to 70C
	Humidity	0% to 95% (non-condensing) at 25C
Physical Characteristics	Color	Black & Silver
	Form Factor	Compact
	Material	Aluminum and Plastic
	Cable Length	11.0 in [2.8 cm]
	Product Length	4.9 in [1.2 cm]
	Product Width	2.7 in [69.000 mm]
	Product Height	1.1 in [27.000 mm]
	Weight of Product	5.2 oz [147.800 g]
Packaging Information	Package Length	7.7 in [2.0 cm]
	Package Width	5.5 in [1.4 cm]
	Package Height	1.5 in [37.000 mm]
	Shipping (Package) Weight	9.5 oz [270.000 g]
What's in the Box	Included in Package	Docking Station
	Included in Package	User Manual

**Product appearance and specifications are subject to change without notice.*