


9829
Max. 19,5 W
AC/DC SWITCH MODE PLUG-IN

- 4,5-12 V eller 12-30 V justerbar utgangsspenning
- Kompakt enhet, lett vekt (135 g)
- Fast ledning, kan leveres med utskiftbare DC plugger
- Leveres med EU eller UK nettilkobling
- 4,5-12 V or 12-30 V user adjustable output voltage
- Compact design and light weight (135 g)
- Fixed cord, exchangeable DC plugs available
- Available with EU or UK plug-in terminals



Tekniske data	Technical specifications	4,5-12 V	12-30 V
Inngangsspenning:	<i>Input voltage:</i>	200-250 VAC	
Utgangsspenning – justerbar:	<i>Output voltage – adjustable:</i>	4,5-12 V	12-30 V
Utg. effekt:	<i>Output voltage:</i>	Max 14.4W	Max 19,5W
Laststrøm:	<i>Load current:</i>	Max. 1.2A	Max. 0,65A
Lastregulering:	<i>Load regulation:</i>	0.5%	
Linjeregulering:	<i>Line regulation:</i>	0.1%	
Sviitsjefrekvens, ca:	<i>Switchfrequency, approx</i>	47kHz	
Effektforbruk, tomgang, ca:	<i>Power consumption at idle, approx</i>	500mW	
Temperaturområde:	<i>Temperature range:</i>	-10°C - +40°C.	
Ripple (typisk):	<i>Ripple (typical):</i>	100mVp-p	
Virkningsgrad:	<i>Efficiency:</i>	>80% at max output power	
Strømbegrensning:	<i>Current limiting:</i>	1,4A ± 0,2A	0,8A ± 0,15A
Isolasjonsklasse:	<i>Insulation class:</i>	II	
Isolasjonsspenning:	<i>Insulation voltage:</i>	3000 VAC / 4242 VDC	
Electrisk sikkerhet:	<i>Electrical safety:</i>	EN 60950	
EMC	<i>EMC standards</i>		
• Emisjon:	• <i>Emission:</i>	EN 61000-6-3	
• Immunitet:	• <i>Immunity:</i>	EN 61000-6-1	
Nettilkobling:	<i>Mains connection:</i>	EU, UK plug-in	
Utgangsterminaler:	<i>Output terminals:</i>	Sekundærkabel secondary cable	
Mål (LxBxH):	<i>Dimensions (LxWxH):</i>	75 x 32 x 50 mm (ex plug)	
Vekt:	<i>Weight:</i>	135 g	

23052006

www.mascot.no
sales@mascot.no
Phone:
Fax:

Main Office
PO Box 177
N-1601 FREDRIKSTAD
NORWAY
+47 69 36 43 00
+47 69 36 43 01

Mascot UK
Box 2090, Salisbury
Wiltshire SP2 2BH
UK
+44 1722 504 853
+44 845 299 1210

Mascot DE-AT-CH-BENELUX
Hirschbergstr. 28/7
D-74838 LIMBACH
GERMANY
+49 6287 95140
+49 6287 95141

Tettnanger Str. 52
D-88239 WANGEN
GERMANY
+49 7528 95 16 77
+49 7528 95 16 78

Mascot France
38 rue Leo Lagrange
94270 Le Kremlin Bicêtre
FRANCE
+33 1 46 58 71 85
+33 1 46 58 71 85