

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2162711062

Status:


Active

Overview:

Off-the-Shelf Cable Assemblies

Description:

SL Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Positive Lock, Single Row, 150.00mm Length, Tin (Sn) Plating, 6 Circuits, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

|                                |                                     |
|--------------------------------|-------------------------------------|
| General                        |                                     |
| Product Family                 | Cable Assemblies                    |
| Series                         | 216271                              |
| Application                    | Signal, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration         | Single Ended Connector              |
| Connector to Connector         | SL-to-Pigtail                       |
| Overview                       | Off-the-Shelf Cable Assemblies      |
| Product Name                   | SL                                  |
| Type                           | Discrete Wire Assembly              |
| UPC                            | 193264731060                        |
| Physical                       |                                     |
| Cable Length                   | 150.00mm                            |
| Circuits (Loaded)              | 6                                   |
| Color - Resin                  | Black                               |
| Gender                         | Female-Pigtail                      |
| Lock to Mating Part            | Yes                                 |
| Material - Metal               | Phosphor Bronze                     |
| Material - Plating Mating      | Tin                                 |
| Material - Plating Termination | Tin                                 |
| Material - Resin               | Polyester Alloy                     |
| Net Weight                     | 5.494/g                             |
| Number of Rows                 | 1                                   |
| Packaging Type                 | Bag                                 |
| Pitch - Mating Interface       | 2.54mm                              |
| Single Ended                   | Yes                                 |
| Termination Interface: Style   | Crimp or Compression                |
| Wire Insulation Diameter       | 1.63mm max.                         |
| Wire Size AWG                  | 22                                  |
| Wire/Cable Type                | UL 11028                            |
| Electrical                     |                                     |
| Current - Maximum per Contact  | 3.0A                                |
| Voltage - Maximum              | 600V AC/DC                          |
| Material Info                  |                                     |
| Reference - Drawing Numbers    |                                     |
| Sales Drawing                  | 2162711060-000                      |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2020)4578-DC (25 June 2020)             |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

216271 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION