


## Data sheet | Item number: 207-1332 **NEW**

Gelbox; for cables; Branch; with gel; 221, 2273 Series; without splicing connectors; Size 2; gray

[www.wago.com/207-1332](http://www.wago.com/207-1332)



RoHS  
Compliant



BOMcheck.net

Color: ■

### Item description

Note on Packaging Unit (PU) and Subpackaging Unit (SPU):

If you order a full PU, you will receive our eco-friendly, sustainable cardboard blisters packed in a shelf-ready box.

If you order a quantity smaller than a full PU, you will receive the eco-friendly, sustainable cardboard blisters without a shelf-ready box.

Please note the system description for the splicing connectors that can be used.

The Benefits for You:

- Easy, fast and safe to use
- Can be used immediately and accessed again later
- Silicon-free
- Label-free
- Suitable for indefinite storage
- The complete system consisting of Gelboxes and WAGO connectors has been VDE-tested and IPX8-certified.

### Data

#### Connection data

Actuation type

Verrastung

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



## Physical data

|        |                      |
|--------|----------------------|
| Width  | 33.6 mm / 1.323 inch |
| Height | 17.8 mm / 0.701 inch |
| Depth  | 45.9 mm / 1.807 inch |

## Mechanical data

|                 |                          |
|-----------------|--------------------------|
| Mounting type   | Fliegende Verbindung     |
| Protection type | IPx8 (2m/2h) gemäß 60529 |

## Material Data

|                  |              |
|------------------|--------------|
| Color            | gray         |
| Housing material | Polypropylen |
| Weight           | 18.4 g       |

## Environmental Requirements

|                                         |               |
|-----------------------------------------|---------------|
| Surrounding air temperature (operation) | -55 ... 85 °C |
| Surrounding air temperature (storage)   | 0 ... 40 °C   |

## Commercial data

|                       |               |
|-----------------------|---------------|
| Packaging type        | BOX           |
| Country of origin     | IT            |
| GTIN                  | 4055143998017 |
| Customs tariff number | 85389099990   |

## Approvals / Certificates

### Country specific Approvals

| Logo                                                                               | Approval                                     | Additional Approval Text | Certificate name |
|------------------------------------------------------------------------------------|----------------------------------------------|--------------------------|------------------|
|  | VDE<br>VDE Prüf- und Zertifizierungsinstitut | EN 60998                 | 400051938        |

## Counterpart

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.

## Downloads

### Documentation

#### Additional Information

|                        |             |               |          |
|------------------------|-------------|---------------|----------|
| Technical explanations | 03-Apr-2019 | pdf<br>2.2 MB | Download |
|------------------------|-------------|---------------|----------|

### System Description


|                                         |             |               |          |
|-----------------------------------------|-------------|---------------|----------|
| System Description 207 Series Gel boxes | 31-Jul-2020 | pdf<br>1.1 MB | Download |
|-----------------------------------------|-------------|---------------|----------|

## Installation Notes


### Installation




Gelbox öffnen.




Verdrahtete Klemme in die Gelbox einlegen.




Verdrahtete Klemme in die Gelbox einlegen.



Gelbox schließen.



Verrastung sicher verschließen.



Wiederzugänglich:

- Gelbox öffnen
- Gel entfernen
- Umverdrahten mit neuen Komponenten

Subject to changes. Please also observe the further product documentation!



Lift the flap and pull the cover perforation forward.



Press in the perforation on the sides.



Tear off the cover from the perforation.



As a counter display: Bend the rear flap at the fold, straighten it and fix it in the cardboard cut-out



If the flap is not required, tear off from the perforation.



Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.