


Datasheet

Stainless Steel Compression Fittings



- Thermocouple installation fittings
- To suit a wide range of mineral insulated and other probe type sensors offered by Farnell
- Male in-line stainless steel compression type with nut & olive

BSP Parallel:

Type	Thread Size	Thread Type	Suits Probe Ø	Manufacturers Code	Order code
St/Steel	1/8"	BSP Parallel	1.0mm	FC-129-D	2770783
St/Steel	1/8"	BSP Parallel	1.5mm	FC-132-D	1633392
St/Steel	1/8"	BSP Parallel	3.0mm	FC-140-D	1633393
St/Steel	1/8"	BSP Parallel	4.0mm	FC-203-D	XF-1381-FAR
St/Steel	1/8"	BSP Parallel	1/8"	FC-139-D	XF-1386-FAR
St/Steel	1/8"	BSP Parallel	3/16"	FC-137-D	XF-1380-FAR
St/Steel	1/4"	BSP Parallel	1.5mm	FC-173-D	XF-1485-FAR
St/Steel	1/4"	BSP Parallel	3.0mm	FC-159-D	2770781
St/Steel	1/4"	BSP Parallel	4.0mm	FC-176-D	XF-1486-FAR
St/Steel	1/4"	BSP Parallel	6.0mm	FC-168-D	1633398
St/Steel	1/4"	BSP Parallel	1/4"	FC-170-D	2770785
St/Steel	1/4"	BSP Parallel	1/8"	FC-161-D	XF-1483-FAR
St/Steel	1/4"	BSP Parallel	3/16"	FC-169-D	XF-1375-FAR
St/Steel	1/2"	BSP Parallel	3.0mm	FC-199-D	2770786
St/Steel	1/2"	BSP Parallel	6.0mm	FC-201-D	2770782
St/Steel	1/2"	BSP Parallel	8.0mm	FC-212-D	XF-1376-FAR

BSPT Tapered:

Type	Thread Size	Thread Type	Suits Probe Ø	Manufacturers Code	Order code
St/Steel	1/8"	BSPT Tapered	1.0mm	FC-130-D	XF-1339-FAR
St/Steel	1/8"	BSPT Tapered	1.5mm	FC-131-D	254630
St/Steel	1/8"	BSPT Tapered	3.0mm	FC-133-D	254642
St/Steel	1/8"	BSPT Tapered	4.0mm	FC-122-D	XF-1481-FAR
St/Steel	1/8"	BSPT Tapered	6.0mm	FC-136-D	XF-1384-FAR
St/Steel	1/8"	BSPT Tapered	1/8"	FC-134-D	XF-1385-FAR
St/Steel	1/8"	BSPT Tapered	3/16"	FC-135-D	XF-1378-FAR
St/Steel	1/4"	BSPT Tapered	1.5mm	FC-164-D	XF-1484-FAR
St/Steel	1/4"	BSPT Tapered	3.0mm	FC-158-D	1633411
St/Steel	1/4"	BSPT Tapered	4.0mm	FC-177-D	XF-1487-FAR
St/Steel	1/4"	BSPT Tapered	6.0mm	FC-167-D	XF-1387-FAR
St/Steel	1/4"	BSPT Tapered	1/4"	FC-165-D	XF-1383-FAR
St/Steel	1/4"	BSPT Tapered	1/8"	FC-160-D	XF-1338-FAR
St/Steel	1/4"	BSPT Tapered	3/16"	FC-163-D	XF-1330-FAR
St/Steel	1/2"	BSPT Tapered	3.0mm	FC-209-D	2770784
St/Steel	1/2"	BSPT Tapered	6.0mm	FC-200-D	1633414
St/Steel	1/2"	BSPT Tapered	8.0mm	FC-210-D	XF-1331-FAR

Type	Thread Type	Pitch	Suits Probe Ø	Manufacturers Code	Order Code
St/Steel	M8	1mm	1.0mm	FC-250-D	XF-1343-FAR
St/Steel	M8	1mm	1.5mm	FC-251-D	XF-1347-FAR
St/Steel	M8	1mm	2.0mm	FC-252-D	XF-1344-FAR
St/Steel	M8	1mm	3.0mm	FC-174-D	XF-1353-FAR
St/Steel	M8	1mm	4.0mm	FC-255-D	XF-1490-FAR
St/Steel	M8	1mm	4.5mm	FC-256-D	XF-1491-FAR
St/Steel	M8	1mm	1/8"	FC-254-D	XF-1489-FAR
St/Steel	M8	1mm	3/16"	FC-257-D	XF-1492-FAR
St/Steel	M16	1.5mm	3.0mm	FC-226-D	2770787
St/Steel	M16	1.5mm	4.5mm	FC-231-D	XF-1488-FAR
St/Steel	M16	1.5mm	6.0mm	FC-223-D	XF-1329-FAR
St/Steel	M16	1.5mm	8.0mm	FC-225-D	XF-1335-FAR
St/Steel	M20	1.5mm	1.5mm	FC-271-D	XF-1493-FAR
St/Steel	M20	1.5mm	3.0mm	FC-273-D	XF-1348-FAR
St/Steel	M20	1.5mm	4.5mm	FC-276-D	XF-1349-FAR
St/Steel	M20	1.5mm	6.0mm	FC-278-D	XF-1350-FAR
St/Steel	M20	1.5mm	8.0mm	FC-280-D	XF-1494-FAR

Type	Thread Size	Thread Type	Suits Probe Ø	Manufacturers Code	Order Code
St/Steel	1/8"	NPT	1.0mm	FC-150-D	XF-1362-FAR
St/Steel	1/8"	NPT	1.5mm	FC-151-D	XF-1361-FAR
St/Steel	1/8"	NPT	2.0mm	FC-148-D	XF-1482-FAR
St/Steel	1/8"	NPT	3.0mm	FC-152-D	XF-1342-FAR
St/Steel	1/8"	NPT	4.0mm	FC-149-D	XF-1379-FAR
St/Steel	1/8"	NPT	4.5mm	FC-154-D	XF-1373-FAR
St/Steel	1/8"	NPT	6.0mm	FC-156-D	XF-1354-FAR
St/Steel	1/8"	NPT	1/8"	FC-153-D	XF-1363-FAR
St/Steel	1/8"	NPT	3/16"	FC-155-D	XF-1372-FAR
St/Steel	1/8"	NPT	1/4"	FC-157-D	XF-1337-FAR
St/Steel	1/4"	NPT	1.5mm	FC-179-D	XF-1371-FAR
St/Steel	1/4"	NPT	4.0mm	FC-186-D	XF-1359-FAR
St/Steel	1/4"	NPT	4.5mm	FC-182-D	XF-1357-FAR
St/Steel	1/4"	NPT	6.0mm	FC-184-D	XF-1358-FAR
St/Steel	1/4"	NPT	8.0mm	FC-185-D	XF-1370-FAR
St/Steel	1/4"	NPT	1/8"	FC-181-D	XF-1356-FAR
St/Steel	1/4"	NPT	3/16"	FC-183-D	XF-1355-FAR
St/Steel	1/4"	NPT	1/4"	FC-187-D	XF-1360-FAR
St/Steel	1/2"	NPT	3.0mm	FC-240-D	XF-1366-FAR
St/Steel	1/2"	NPT	4.5mm	FC-241-D	XF-1367-FAR
St/Steel	1/2"	NPT	6.0mm	FC-242-D	XF-1368-FAR
St/Steel	1/2"	NPT	8.0mm	FC-243-D	XF-1364-FAR
St/Steel	1/2"	NPT	1/8"	FC-245-D	XF-1336-FAR
St/Steel	1/2"	NPT	3/16"	FC-246-D	XF-1365-FAR
St/Steel	1/2"	NPT	1/4"	FC-247-D	XF-1369-FAR