

**RoHS Compliant**

## PX-313/PX-303

### PCIe 2xRS422/485 1MBaud

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



#### Description

PCI Express Card providing two RS422/485 serial ports. Up to 921,600 data transfer rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows 2000, XP, Server 2003, Vista, Server 2008, Windows 7 and Windows 8.

PCI Express is the latest standard in PC connectivity.

With Brainboxes' industry renowned Lifetime Warranty and Lifetime Support!

#### Features

- 2 port RS422/485
- PCI Express x1, x4, x8 x16 lane slots socket size
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

#### Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- Windows Server 2003 32 bit 64 bit Editions

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



#### Options



PX-313:  
PCIe 2xRS422/485  
1MBaud

PX-303:  
PCIe 1 + 1xRS422/485  
1MBaud


#### ORDER

Description

PCIe 2xRS422/485 1MBaud  
PCIe 1 + 1xRS422/485 1MBaud

Code

PX-313  
PX-303



## PCIe 2xRS422/485 1MBaud

### PX-313/PX-303: Full Specification

<p><b>Port</b></p> <table border="1"> <tr><td>Pin 1</td><td>TXD-</td></tr> <tr><td>Pin 2</td><td>TXD+</td></tr> <tr><td>Pin 3</td><td>RTS-</td></tr> <tr><td>Pin 4</td><td>RTS+</td></tr> <tr><td>Pin 5</td><td>GND</td></tr> <tr><td>Pin 6</td><td>RXD-</td></tr> <tr><td>Pin 7</td><td>RXD+</td></tr> <tr><td>Pin 8</td><td>CTS-</td></tr> <tr><td>Pin 9</td><td>CTS+</td></tr> </table> <p>RS422/485 Pinout (9 Pin)</p>	Pin 1	TXD-	Pin 2	TXD+	Pin 3	RTS-	Pin 4	RTS+	Pin 5	GND	Pin 6	RXD-	Pin 7	RXD+	Pin 8	CTS-	Pin 9	CTS+	<p>Ports</p> <p>Connector</p> <p>FIFO size</p> <p>Operating Distance</p> <p>Cable</p>	<p>2 x RS422/485</p> <p>DB9 Connector - 9 Pin Male</p> <p>128 RX FIFO + 128 TX FIFO</p> <p>RS422/485 Standard 4000 ft : 1200 metres</p> <p>No Cable; Integrated Connector</p>
Pin 1	TXD-																			
Pin 2	TXD+																			
Pin 3	RTS-																			
Pin 4	RTS+																			
Pin 5	GND																			
Pin 6	RXD-																			
Pin 7	RXD+																			
Pin 8	CTS-																			
Pin 9	CTS+																			
<p><b>Port Settings</b></p> <p>921,600            baud</p>	<p>Baud Rate</p> <p>Data Bits</p> <p>Parity</p> <p>Stop Bits</p> <p>Flow Control</p> <p>Tx/Rx Modes</p>	<p>921,600</p> <p>5,6,7 or 8</p> <p>Odd, Even, None, Mark or Space</p> <p>1, 1.5 or 2</p> <p>RTS/CTS, DSR/DTR, XON/XOFF</p> <p>Full Duplex, Half Duplex Autogating - Hardware Autogating</p>																		
<p><b>Interface</b></p>	<p>OS Compatibility</p> <p>BUS</p>	<p>Microsoft Windows 8 32 bit 64 bit Editions          Microsoft Windows 7 32 bit 64 bit Editions          Windows Server 2008 32 bit 64 bit Editions          Windows Vista 32 bit 64 bit Editions          Windows Server 2003 32 bit 64 bit Editions</p> <p>PCI Express x1, x4, x8 x16 lane slots</p>																		
<p><b>Approvals</b></p>	<p>Other Approvals</p> <p>Microsoft Approvals</p>	<p>AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA</p> <p>Windows 7 32 bit 64 bit Editions          Windows Vista 32 bit 64 bit editions          Windows Server 2003 32 bit 64 bit editions          Windows XP 32 bit 64 bit editions</p>																		
<p><b>General</b></p>	<p>PCB Layers</p> <p>Power Consumption</p> <p>Weight</p> <p>Size</p>	<p>4</p> <p>380mA @ 3.3V</p> <p>0.064 kg</p> <p>105l x 18w x 120h mm</p>																		
<p><b>Box Content</b></p>	<p>Packaging</p> <p>Card</p>	<p>Installation CD including manual, Microsoft signed drivers &amp; utilities</p> <p>PCIe 2xRS422/485 1MBaud</p> <p>No Cable; Integrated Connector</p>																		
<p><b>Product Support</b></p>	<p>Warranty</p> <p>Support</p>	<p>Lifetime (online registration required)</p> <p>Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team</p>																		
<p><b>Additional</b></p>	<p>OEM option</p> <p>Made In</p> <p>Customisable</p>	<p>Available for bulk buy OEM</p> <p>Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"</p> <p>Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: <a href="mailto:sales@brainboxes.com">sales@brainboxes.com</a></p>																		