

# **XLR CABLE CONNECTORS**

## **5 PIN XLR**

5 pin XLR style connectors perfect for use in audio cables and also in DMX cables.

### **SPECIFICATIONS**

PRODUCT

Gender: Male (IO-XLR5-M-BK)

Female (IO-XLR5-F-BK)

Contacts: 5

#### ELECTRICAL

Capacitance Between Contacts: < 2 pF

Capacitance Between Contact and Ground: < 2 pF

Contact Resistance: < 7 mΩ

Insulation Resistance: ≥ 1000 MΩ

Dielectric Strength: 1500V @ 60s

Current Rating: 7.5 A / 125 V AC

#### ENVIRONMENTAL

UL Flammability Rating: UL 94 HB Standard Compliance: IEC 61076-2-103 Temperature Range: -40°C ~ +70° C (-40°F ~ +158°F)



IO-XLR5-M-BK IO-XLR5-F-BK

#### MECHANICAL

Lifetime: > 1000 Mating Cycles Cable O.D.: 3.5 - 8.0mm Wiresize: 1.25mm OD Max Wiring: Solder Contacts Solderability: Complies with IEC 60068-2-20 MATERIAL Pins: Brass (IO-XLR5-M-BKAU) Phosphor Bronze (IO-XLR5-F-BKAU) Pin Plating: Silver Push Button: Die Cast Zinc Locking Mechanism: Stainless Steel Locking Mechanism Finish: Tin Shell: Die Cast Zinc Shell Finish: Black Insert: POM

Bushing: PVC

Product specifications may change without prior notification


Io Audio Technologies® is a registered trademark of Knight Electronics, Inc. 10557 Metric Dr. Dallas, TX 75243 | 214-340-0265 | 800-323-2439 | Fax: 214-340-5870 | www.ioaudiotechnologies.com





# DRAWINGS

### IO-XLR5-M-BK









# **FEATURES & APPLICATIONS**

The IO-XLR5-M-BK and IO-XLR5-F-BK connectors feature durable die cast zinc shells with built in latch locks which provide a reliable connection when mated with the opposite gender. They also feature a sturdy plastic insert that tightens onto the cable to provide strain relief while an additional rubber boot delivers extended support from excessive bending. The silver plated contacts ensure a great signal every time.

5 pin XLR connectors are a perfect solution for applications requiring a rugged and dependable locking connection. Because the housing construction is threaded, the connectors require no tools for assembly, making them ideal for onsite termination and allow the user to be able to troubleshoot connection issues quickly. This connector is perfect for use in balanced audio, DMX, low voltage power, and control applications where the termination method is solder cups.

These connectors are also available with gold plated contacts (IO-XLR5-M-BKAU & IO-XLR5-F-BKAU).

### PART NUMBER BREAKDOWN:

IO-XLR5-M-BK Connector Type IO-XLR5-M-BK Number of Pins IO-XLR5-M-BK Gender IO-XLR5-M-BK Body Color

### **STANDARDS & CLASSIFICATIONS**



Product specifications may change without prior notification

Io Audio Technologies® is a registered trademark of Knight Electronics, Inc. 10557 Metric Dr. Dallas, TX 75243 | 214-340-0265 | 800-323-2439 | Fax: 214-340-5870 | www.ioaudiotechnologies.com