

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC), 20M (65.61 ft.)

MODEL NUMBER: N320-20M



Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber
- Insertion loss testing performed on every connector (0.2dB typical)

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 20-meter (66ft) Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Duplex multimode fiber is most commonly used in LAN applications
- Fiber optic distributed data interface (FDDI) rated and OFNR (riser rated)

Specifications

OVERVIEW	
UPC Code	037332125712
Clad Diameter	125 micron
Core Diameter	62.5 micron
Number of Fibers	2
Technology	Multimode
Optical Mode	OM1
INPUT	
Cable Length (ft.)	65.6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	20
Cable Length (in.)	787.4
PHYSICAL	
Color	Orange
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.16
Shipping Weight (lbs.)	0.35
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	LC DUPLEX (MALE)
SPECIAL FEATURES	
Push/Pull Tabs	No
STANDARDS & COMPLIANCE	
Approvals	FDDI and OFNR rated
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>