





#23637

Full HD Webcam

Full HD webcam with 1080p resolution for clear video calling

Key features

- · All-in-one webcam with premium audio and video quality
- Upgrade your webcam experience: wide angle, high resolution and versatile placement
- Sharp video: full HD 1080p resolution and auto-focus
- Automatic white balance for clear video in any light condition
- Works with Skype and other video calling software
- Use with any PC or laptop



What's in the box

- Webcam
- Tripod stand
- User guide



FULL HD 1080P QUALITY

System requirements

- Windows 10, 8 or 7
- Intel-based Mac with Mac OS X 10.15 (Catalina) or higher
- Chrome OS
- USB port















Comfortable Conferencing

What if you could put an end to awkward, low-lit, fuzzy sounding conference calls? At a time when you want to be able to connect in the best way possible via video, the Trust Tyro Full HD Webcam offers the solution; all the features that make video calling and video streaming that much more comfortable are packed into one device.

Look and Sound Your Best

With premium audio and video quality, rest assured that you will look and sound great on every call and video stream, regardless of where you are. The full HD 1080p resolution wide angle lens and auto-focus ensure razor-sharp video, while the automatic white balance offers outstanding low-light performance, for clear video in any condition.





Easy to Use

With a plug & play setup, video calling has never been easier; once the USB receiver has been plugged into your PC or laptop, you can start calling straight away. The Trust Tyro Full HD Webcam works with Zoom, Teams, Skype and other video calling software. The webcam clips easily onto your monitor, sits nicely on a desk and also comes with a tripod stand, making this ideal device versatile enough to suit any office or home office setup.





Tyro Full HD Webcam

GE	N	Ε	R/	AL
----	---	---	----	----

Plug & play **Driver needed** False True

Mounting type Tripod Height of main product 35 mm (in mm)

Width of main product 115 mm

Depth of main product 80 mm (in mm) (in mm)

Total weight 153 g Weight of main unit 80 g

LIGHTING

Lights False

CONNECTIVITY

USB version 2.0 Cable length main cable 150 cm

MICROPHONE

Noise reduction False

IMAGING

Sensor resolution 1920 x 1080 **Max Framerate** 30 fps

Still image resolution 1920 x 1080 **Video resolution** 1920 x 1080 **Snapshot button** False Viewing angle 64 degrees

Automatic white balance True **Face tracking** False

Focus distance 45 - 10000 mm Auto focus Focus type

Motion detection False Zoom type Digital

Privacy mode False

AUDIO

Microphone built-in True

COMPATIBILITY

Compatible Device Types Laptop, pc **Compatible Software** Chrome OS, Mac OS,

Platforms Windows

FEATURES

Software False



Tyro Full HD Webcam



PRODUCT VISUAL 1



PRODUCT PICTORIAL 1



PRODUCT PICTORIAL 2



PRODUCT PICTORIAL 3



PRODUCT ESHOT 1



PRODUCT FRONT 1



PRODUCT FRONT 2



PRODUCT EXTRA 1



PRODUCT EXTRA 2



PRODUCT SIDE 1



PACKAGE VISUAL 1

Item number: 23637

URL: www.trust.com/23637 EAN Code: 8713439236378



PACKAGE FRONT 1

