





PRODUCT DATA SHEET

EVERBUILD® Lumberjack® 30 Min PU Wood Adhesive

PROFESSIONAL QUALITY 1-PART MOISTURE CURING WOOD ADHESIVES WITH RAPID SETTING PROPERTIES

PRODUCT DESCRIPTION

EVERBUILD® Lumberjack® 30 Min PU Wood Adhesive is a professional quality one part moisture curing wood adhesive, which sets hard in 30 minutes. As well as bonding all common wood types (hard, soft, exotic, painted) EVERBUILD® Lumberjack® 30 Min PU Wood Adhesive will also bond Formica, polystyrene, PU foam metal and glass wool and various plastics (including PVC) to porous surfaces. Also adheres to stone, concrete, brick and masonry.

USES

- General wood jointing and construction
- Window and door frame manufacture
- Door manufacture
- Furniture manufacture
- Construction of staircases and ladders
- As a high quality insulation adhesive for foam/glasswool/fibre boarding

CHARACTERISTICS / ADVANTAGES

- Fast setting 30 minute set (Typical PVA based wood glue – 8-12 hours)
- Exceptional bond strength to wood and most common building surfaces.
- Internal and external use excellent weathering and aging properties.
- Products foam slightly on application to fill small gaps and increase overall bond strength.
- Excellent Chemical Resistance.

Contents	100% prepolymers and
	catalyst (solvent free)
Viscosity	200 x10 ³ mPa.s (bfld RVT
	sp7 5rpm) (gel)

APPROVALS / STANDARDS

Fully waterproof to EN204 D4

PRODUCT INFORMATION

Packaging	310ml cartridge and 750 g plastic bottle
Colour	Gel - Transparent Liquid - Brown
Shelf Life	Twelve months from date of manufacture in original unopened containers.
Storage Conditions	Store in original unopened containers between 5 and 25°C. Reseal immediately once used or disposal will be necessary.
Solid content by weight	100% (solvent free)
Consistency	Gel or liquid

Product Data Sheet EVERBUILD® Lumberjack® 30 Min PU Wood Adhesive February 2018, Version 01.01 020513010000000049 225-355ml/m², or 10 linear meters per tube (approx)

APPLICATION INSTRUCTIONS

SUBSTRATE PREPARATION

The surfaces to be glued should be clean and free from dust, grease and other contaminants. At least one of the materials must be porous. Roughen non-porous surfaces to give a key for the adhesive. To assist cure and achieve maximum bond strength, slightly moisten one surface with a damp cloth. Do not over wet.

APPLICATION METHOD / TOOLS

Cartridge Products: Cut tip of cartridge taking care not to damage the thread. Fix nozzle, cut to required aperture and apply using standard sealant gun. Liquid version: Remove cap, cut spout and apply. Replace cap after use.

Wearing of gloves is recommended. Apply adhesive evenly to one surface. If necessary, cover large areas with a fine toothed spreader. Assemble parts IMMEDIATELY and clamp for duration of cure (5-30 minutes at 20°c; longer at lower temperatures). After this time, the joint may be easily handled. Full and final bond strength will be achieved after 30 minutes for 5 minute set or 24 hours for 30 minute set.

NOTE: These products foam slightly on application to fill small gaps. Any excess foam/adhesive must be removed with acetone before the product sets or with a sharp chisel once set.

CLEANING OF TOOLS

Everbuild Dual Purpose Foam Cleaner or acetone BE-FORE curing. After cure, use mechanical abrasion.

LIMITATIONS

- At least one of the surfaces to be bonded must be porous.
- Not suitable for polyethylene, polypropylene, Teflon or Nylon.
- Surfaces may be damp, but moisture content of wood must not exceed 30%w/w.
- As product expands slightly on curing, do not use on sheet laminate. Use STICK 2 CONTACT ADHESIVE.
- Only apply between + 5 and + 30°C.
- Ensure surfaces are always clamped during use.
- Setting times will be increased at low temperatures and low humidity.

VALUE BASE

All technical data stated in this Data Sheet are based on laboratory tests. Actual measured data may vary due to circumstances beyond our control.

LOCAL RESTRICTIONS

Note that as a result of specific local regulations the declared data and recommended uses for this product may vary from country to country. Consult the local Product Data Sheet for the exact product data and

ECOLOGY, HEALTH AND SAFETY

Consult MSDS for full list of hazards.





Product Data Sheet EVERBUILD® Lumberjack® 30 Min PU Wood Adhesive February 2018, Version 01.01 020513010000000049

LEGAL NOTES

The information, and, in particular, the recommendations relating to the application and end-use of Sika products, are given in good faith based on Sika's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with Sika's recommendations. In practice, the differences in materials, substrates and actual site conditions are such that no warranty in respect of merchantability or of fitness for a particular purpose, nor any liability arising out of any legal relationship whatsoever, can be inferred either from this information, or from any written recommendations, or from any other advice offered. The user of the product must test the product's suitability for the intended application and purpose. Sika reserves the right to change the properties of its products. The proprietary rights of third parties must be observed. All orders are accepted subject to our current terms of sale and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.

EVERBUILD BUILDING PRODUCTS LTD

Site 41, Knowsthorpe Way Cross Green Industrial Estate Leeds, LS9 0SW Tel: 0113 240 3456 Web: www.everbuild.co.uk Twitter: @everbuild

SIKA LIMITED

Watchmead Welwyn Garden City Hertfordshire, AL7 1BQ Tel: 01707 394444 Web: www.sika.co.uk Twitter: @SikaLimited

SIKA IRELAND LIMITED

Ballymun Industrial Estate Ballymun Dublin 11, Ireland Tel: +353 1 862 0709 Web: www.sika.ie Twitter: @Sikalreland

EVERBUILDLumberjack30MinPUWoodAdhesive-en-GBEVER-(02-2018)-1-1.pdf



