





## PRODUCT DATA SHEET

# EVERBUILD® ROLL & STROLL® Contract Carpet

#### A CLEAR SELF ADHESIVE CARPET PROTECTOR

#### PRODUCT DESCRIPTION

EVERBUILD® ROLL & STROLL® Contract Carpet is a clear self adhesive carpet protection system. With the adhesive coating on the outside Roll & Stroll Contract Carpet Protector is easy to unwind, safer than dust-sheets and has a multitude of uses across all trade sectors. Totally waterproof Roll & Stroll Contract Carpet Protector protects against paint spillage, and is tough enough not to tear or rip. Clear Branded Film.

#### **USES**

EVERBUILD® ROLL &STROLL® Contract Carpet is ideal for protecting stair carpets and can be used for commercial and domestic applications.

### **CHARACTERISTICS / ADVANTAGES**

- Easy roll out with no specialist applicator equipment required.
- Will not creep and wrinkle after application. Stays where it is put!
- Totally waterproof.
- Protects against expensive to clean spillages from paints, varnishes etc.
- Easily removed, will not leave a sticky residue.
- Can be left for up to 4 weeks \*.
- Adheres to most common hard surfaces.
- Safer than dust sheets.

Adhesive	pressure sensitive acrylic.
Adhesive strength	1000 - 1300 g/50mm

#### **PRODUCT INFORMATION**

Packaging	50m & 100m roll
Appearance / Colour	Clear film
Shelf Life	36 months from Date of manufacture.
Storage Conditions	Store in cool dry conditions between 5 and 25°C. Safe in normal use however as a precaution keep polythene outer packaging away from children.
Thickness	60 ± 5 μm

#### **APPLICATION INSTRUCTIONS**

#### **SUBSTRATE PREPARATION**

Ensure surfaces to which EVERBUILD® ROLL &STROLL® Contract Carpet is to be applied are clean, dust free and dry.

#### **APPLICATION METHOD / TOOLS**

Remove outer packaging from roll. Place roll on the floor facing the direction it is to be applied and unwind approx 12 inches (300mm) of material. Ensure the roll is stuck by smoothing out by either hand or foot. Simply push roll forward using hands or feet en-

Product Data Sheet EVERBUILD® ROLL &STROLL® Contract Carpet January 2019, Version 01.02 0205160500000000052 suring roll goes in a straight line. Smooth out with hands or feet as it unwinds. A very effective way of laying Roll and Stroll is to push the roll along with a soft broom/brush using the brush to smooth out and remove air bubbles as it unwinds.

#### **LIMITATIONS**

- This product is for application to carpets, DO NOT use on hard surfaces. Use Roll and Stroll Hard Surface Protector.
- Adhesion will be reduced on dusty surfaces. Vacuuming or mopping prior to use is recommended.
- EVERBUILD® ROLL &STROLL® Contract Carpet must be removed after a maximum of 4 weeks to prevent a sticky residue being left.
- Always check EVERBUILD® ROLL &STROLL® Contract Carpet is stuck firmly to surfaces before commencing work.
- Not suitable for pure wool carpet
- On some surfaces EVERBUILD® ROLL &STROLL® Contract Carpet may leave a residue, this can be easily removed using Everbuild Wonder Wipes or warm soap and water. A test area is always recommended prior to full application. Always check compatibility of cleaning agent with sub floor prior to full application.
- \*In heavily trafficked areas or where air temperature exceeds 22°C, remove after 1 week maximum. Do not use underfloor heating whilst product is in situ.
- Do not use on surfaces which bleed oils or plasticizers.
- Product may become slippery when wet. Mop up any spills immediately or replace where necessary.
- It is the users responsibility to determine suitability for use. If in doubt contact technical services for advice.

#### **VALUE BASE**

All technical data stated in this Data Sheet are based on laboratory tests. Actual measured data may vary due to circumstances beyond our control.

#### **LOCAL RESTRICTIONS**

Note that as a result of specific local regulations the declared data and recommended uses for this product may vary from country to country. Consult the local Product Data Sheet for the exact product data and uses.

#### **ECOLOGY, HEALTH AND SAFETY**

Consult MSDS for full list of hazards.

#### **LEGAL NOTES**

The information, and, in particular, the recommendations relating to the application and end-use of Sika products, are given in good faith based on Sika's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with Sika's recommendations. In practice, the differences in materials, substrates and actual site conditions are such that no warranty in respect of merchantability or of fitness for a particular purpose, nor any liability arising out of any legal relationship whatsoever, can be inferred either from this information, or from any written recommendations, or from any other advice offered. The user of the product must test the product's suitability for the intended application and purpose. Sika reserves the right to change the properties of its products. The proprietary rights of third parties must be observed. All orders are accepted subject to our current terms of sale and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.

#### EVERBUILD BUILDING PRODUCTS LTD

Site 41, Knowsthorpe Way Cross Green Industrial Estate Leeds, LS9 0SW Tel: 0113 240 3456 Web: www.everbuild.co.uk Twitter: @everbuild

#### SIKA LIMITED

Watchmead Welwyn Garden City Hertfordshire, AL7 1BQ Tel: 01707 394444 Web: www.sika.co.uk Twitter: @SikaLimited

#### SIKA IRELAND LIMITED

Ballymun Industrial Estate Ballymun Dublin 11, Ireland Tel: +353 1 862 0709 Web: www.sika.ie Twitter: @Sikalreland







Product Data Sheet EVERBUILD® ROLL &STROLL® Contract Carpet January 2019, Version 01.02 0205160500000000052



EVERBUILDROLLSTROLLContractCarpet-en-GBEVER-(01-2019)-1-2.pdf