

# Terminal Kit

**multicomp** PRO

**RoHS  
Compliant**



### Specifications:

Connector Type : Female Disconnect  
Termination Method : Crimp  
Contact Material : Brass

### Specifications Table:

Part Number	Description	Tab Size (Inches)	AWG	Colour	Qty. in Kit
MC29396	Nylon-Fully Insulated Double Crimp Female Disconnects	0.032 × 0.25	22 to 16	Red	15
MC29395		0.02 × 0.187			
MC29398		0.032 × 0.25	16 to 14	Blue	
MC29397		0.02 × 0.187			




### Specifications:

Connector Type : Male & Female Disconnect  
Termination Method : Crimp  
Contact Material : Brass

### Specifications Table:

Part Number	Description	Tab Size (Inches)	AWG	Colour	Qty. in Kit
MC29390-1	Nylon-Fully Insulated Female & Male Disconnect	0.032 × 0.25	22 to 16	Clear	15
MC29390-2			16 to 14		



### Specifications:

Connector Type : Disconnect  
Termination Method : Crimp  
Contact Material : Brass  
Contact Plating : Tin

### Specifications Table:

Part Number	Description	Tab Size (Inches)	AWG	Colour	Qty. in Kit
MC29390-3	Nylon-Insulated Double Crimp Flag Female Disconnects (With Short Copper Sleeve)	0.032 × 0.25	22 to 18	Red	12
MC29390-4		0.02 × 0.187			
MC29390-5		0.032 × 0.25	16 to 14	Blue	

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO

# Terminal Kit

**multicomp** PRO



### Specifications:

Connector Type : Disconnect  
 Termination Method : Crimp  
 Contact Material : Brass

### Specifications Table:

Part Number	Description	Tab Size (Inches)	AWG	Colour	Qty. in Kit
MC29390-6	Vinyl-Insulated Double Crimp Female Disconnects	0.02 × 0.110	22 to 16	Red	15
MC29390-7		0.02 × 0.187	22 to 16		
MC29646		0.032 × 0.25	16 to 14	Blue	
MC29390-8		0.032 × 0.25	12 to 10	Yellow	



### Specifications:

Connector Type : Butt Splice  
 Termination Method : Crimp  
 Contact Material : Copper  
 Contact Plating : Tin  
 Insulator Material : Vinyl

### Specifications Table:

Part Number	Description	Tab Size (Inches)	AWG	Colour	Qty. in Kit
MC29374	Vinyl-Insulated Butt Splice Connectors	-	22 to 16	Red	15



### Specifications Table:

Part Number	Description	Tab Size (Inches)	AWG	Colour	Qty. in Kit
MC29390-9	Vinyl-Insulated Changing Down Butt Splice Connectors	-	16 to 14 22 to 18	Blue w/ Red Colour Ring	15



### Specifications Table:

Part Number	Description	Tab Size (Inches)	AWG	Colour	Qty. in Kit
MC29390-10	Closed End Connectors (Inside Sleeve Is Copper Tube)	-	22 to 16	Clear	15

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro

**multicomp** PRO

# Terminal Kit



## Specifications Table:

Part Number	Description	Tab Size (Inches)	AWG	Colour	Qty. in Kit
MC29390-11	Nylon-Insulated Spade Terminals (Butted Seam)	#6	16 to 14	Blue	15
MC29390-12			22 to 16	Red	

## Crimping tool



## Specifications

- 8-1/4" 6 ways crimping tool
- Wire Cutter
- Crimps Insulated Terminals
- Crimps Non-Insulated Terminals
- Crimps Ignition 7mm to 8mm
- Bolts Cutter
- Wire Stripper
- Handle : 22-16 AWG  
16-14 AWG  
12-10 AWG

## Specifications Table:

Part Number	Description	Qty. in Kit
MC299	Crimp Tool	1

## Part Number Table

Description	Part Number
Terminal Kit, 262PC, Crimp Tool	MCK19

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.