



Quality Products. Service Excellence.

Locking Doors *RSD Series*

For use with the REFK, 1564 and RS Cabinet Series

Features:



- 16-gauge steel construction.
- Mounts either right or left hand hinge (door & cabinet are symmetrical).
- Includes installed lock and two keys.
- Finished in rugged textured powder paint to match **REFK enclosure series**.
- Stocked in Black & Light Gray (RAL7035).
- Includes mounting hardware.



Solid Doors

Part No. Black	Part No. RAL 7035 Light Gray	Height	Use With REFK Frame Rack Units	Part No.
RSDF19035BK1	RSDF19035LG1	35.00	20U	REFK1903524
RSDF19042BK1	RSDF19042LG1	42.00	24U	REFK1904224
RSDF19049BK1	RSDF19049LG1	49.00	28U	REFK1904924
RSDF19056BK1	RSDF19056LG1	56.00	32U	REFK1905624
RSDF19063BK1	RSDF19063LG1	63.00	36U	REFK1906324
RSDF19070BK1	RSDF19070LG1	70.00	40U	REFK1907024
RSDF19077BK1	RSDF19077LG1	77.00	44U	REFK1907724

Louvered Doors

Part No. Black	Part No. RAL 7035 Light Gray	Height	Use With REFK Frame Rack Units	Part No.
RSDL19035BK1	RSDL19035LG1	35.00	20U	REFK1903524
RSDL19042BK1	RSDL19042LG1	42.00	24U	REFK1904224
RSDL19049BK1	RSDL19049LG1	49.00	28U	REFK1904924
RSDL19056BK1	RSDL19056LG1	56.00	32U	REFK1905624
RSDL19063BK1	RSDL19063LG1	63.00	36U	REFK1906324
RSDL19070BK1	RSDL19070LG1	70.00	40U	REFK1907024
RSDL19077BK1	RSDL19077LG1	77.00	44U	REFK1907724

Window Doors

Part No.	Use With REFK Frame
----------	---------------------

Black	Height	Rack Units	Part No.
Black	Height	Rack Units	Part No.
REDFP19035BK1	35.00	20U	REFK1903524
REDFP19042BK1	42.00	24U	REFK1904224
REDFP19049BK1	49.00	28U	REFK1904924
REDFP19056BK1	56.00	32U	REFK1905624
REDFP19063BK1	63.00	36U	REFK1906324
REDFP19070BK1	70.00	40U	REFK1907024
REDFP19077BK1	77.00	44U	REFK1907724

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.