Hand Held Digital Multimeter Multicomp PRO



Features

- True RMS
- · Data hold/backlight
- · Max/Min/Relative mode
- USB communication
- Input protection
- Diode/continuity test
- NCV (audible/visual alarm)
- LoZ ACV
- Peak Hold

Specifications		
Certifications	CE	
Safety Ratings	CAT III 1000V/CAT IV 600V	
AC voltage (V)	1000V	±(1% +3)
DC voltage (V)	1000V	±(0.5% +3)
AC current (A)	20A	±(1.2% +5)
DC current (A)	20A	±(1% +2)
Resistance (Ω)	60ΜΩ	±(1% +2)
Capacitance (F)	60mF	±(3% +5)
Frequency (Hz)	10MHz	±(0.1% +4)
Duty cycle (%)	0.1% to 99.9%	±(2% +5)
Temperature (°C/°F)	-40°C to 1000°C	±(1% +3)
	-40°F to 1832°F	±(1% +6)
Display count		6000
Bandwidth (Hz)		40Hz to 1kHz
Analog bar		31

General Characteristics

Power : 1.5V Battery (R03) × 4

Product Net Weight : 350g

Product Size : 190mm × 90mm × 50mm

Standard Accessories : Battery, Gold plated Test Leads, USB cable,

Temperature Probe, English manual

RoHS

Compliant

Standard Warranty : 12 Months

Part Number Table

Description	
Hand Held Digital Multimeter, 1000V AC/DC, 20A AC/DC, 60MΩ, 60mF, 10MHz, -40°C to +1000°C	MP730678

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Page <1> 04/03/21 V1.0