

PRODUCT SPECIFICATION

CKI: Carl Kammerling International Ltd.

Brand	C.K
Product Range	Sabretooth saws
Catalogue number	810
Date	15/01/2008

Range Description
High performance hand saw range

- Features**
- Sabretooth 1st cut saws offer the best cutting performance of any of the leading saws on the UK market
 - Triple edge, ultra sharp diamond ground teeth that cut on both the push and the pull, result in up to 41% fewer strokes, saving time and effort*
 - Easy start tooth configuration for clean and accurate cut starts
 - Induction hardened teeth for outstanding wear resistance
 - Rigid 1mm thick blade made from premium quality alloy steel for non flex and perfect straight cuts
 - Hard, smooth and durable blade coating for low friction and protection
 - Ergonomic handle design featuring a soft grip insert for comfort and control plus 45/90 degree marking bevels for convenience
 - First fix and Second fix options available for coarse and fine cutting work
 - Colour coded International packaging for simple product identification
 - POS merchandising solution to drive sales



*1st fix saw tested against other leading saws in independent CATRA tests

Item Number	Item Description	EAN No	Commodity code	Carton Qty
481001	Sabretooth saw 1 st Fix 7 TPI (8 point)	5013969810011	82021000	10
481002	Sabretooth saw 2 nd Fix 11TPI (12 point)	5013969810028	82021000	10
581001	Sabretooth saw 1 st Fix 7 TPI counter box of 10	5013969810035	82021000	10

581002	Sabretooth saw 2 nd Fix 11 TPI counter box of 10	5013969810042	82021000	10
--------	---	---------------	----------	----

Technical product information	<p>Blade Material - SK5 Alloy steel</p> <p>Teeth 3 edge diamond ground, induction hardened to the optimum level to give maximum blade life and prevent tooth breakage</p> <p>Handle Black plastic injection moulded with Yellow TPE soft grip overmould Handle assembly ultrasonically welded for security</p> <p>Application</p> <p><i>First fix</i> 7 Teeth per inch – 8 points Designed for coarse, fast cutting of Timber, Hardboard, Chipboard, MDF, PVC and Plastic</p> <p><i>Second Fix</i> 11 Teeth per inch – 12 points Designed for fine, clean edge cutting of planed and moulded wood, Hardboard, MDF, PVC and Plastic</p>
Standards compliance	None applicable
User health and safety information	Users are advised to wear safety goggles and protective gloves
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	The Sabretooth saws are guaranteed for life against imperfect materials or workmanship The teeth will wear in use and such wear is not covered under the terms of the warranty
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
481001	650	35	145	490	650	36	145	535
481002	650	35	145	490	650	36	145	535
581001								
581002								

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
481001	660	210	160	5850	8	5
481002	660	210	160	5850	8	5
581001	660	210	160	5920	8	5
581002	660	210	160	5920	8	5

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
481001			45	Sleeve			465	Carton
481002			45	Sleeve			465	Carton
581001			450	Sleeves	40	Outer wrap	570	Carton
581002			450	Sleeves	40	Outer wrap	570	Carton