

# **Product datasheet** DULUX D 10 W/830

OSRAM DULUX D | CFLni, 2 tubes, with 2-pin base for CCG operation



 Offices, public buildings Shops Supermarkets and department stores Hotels, restaurants Industry

- Extremly economical Good quality of light Excellent luminous flux Long service life Improved maintenance



#### Technical data


#### **Electrical data**

Nominal wattage	10.00 W
Rated wattage	10.00 W
Operating frequency	50 Hz

#### Photometrical data

Nominal luminous flux	600 lm
Nominat tuninous itux	600 till
Light color (designation)	LUMILUX Warm White
Luminous flux at	600 lm
Rated luminous flux	600 lm
Rated color temperature	3000 K
Rated LLMF at 2,000 h	0.85
Rated LLMF at 4,000 h	0.78
Rated LLMF at 6,000 h	0.76
Rated LLMF at 8,000 h	0.75
Color rendering index Ra	≥80
Color temperature	3000 K
Luminous flux	600 lm
Color rendering index Ra	8089

# Dimensions & weight



Diameter	12.0 mm
Overall length	108.0 mm
Length	110.0 mm
Length acc. to IEC standard	95 mm
Length with base excl. base pins/connection	87.00 mm
Outer bulb	T12X2

Product weight	34.00 g
Maximum diameter	11.0 mm

## Lifespan

Rated lamp life time	10000 h
Service life	6500 h
Rated lamp survival factor at 2,000 h	0.99
Rated lamp survival factor at 4,000 h	0.99
Rated lamp survival factor at 6,000 h	0.95
Rated lamp survival factor at 8,000 h	0.81
Operation mode LLMF/LSF	50 Hz
Lifespan	10000 h <sup>1)</sup>
Nominal lamp life time	10000 h

<sup>1)</sup> With CCG/LLCG

## Additional product data

Base (standard designation)	G24d-1	
Mercury content	1.3 mg	
Appropriate disposal acc. to WEEE	Yes	

# Capabilities

Dimmable	No
Suitable for indoor	Yes


#### Certificates & standards

Energy efficiency class	В
Energy consumption	13 kWh/1000h

# **Country specific categorizations**

ILCOS	FSQ-10/830-I-G24d-1
Order reference	DULUX D 10W/830

# **Light Distribution**



FL\_830

# Equipment / Accessories

- Suitable for operation on conventional control gear

SINGLE LAMP WITH PLUG-IN CONTROL GEAR

SINGLE LAMP WITH CONTROL GEAR

## Logistical Data

Product code Product description Packagii (Pieces/	, ,	Volume	Gross weight
---	-----	--------	--------------

4050300025681	DULUX D 10 W/830	10 Pieces Folding	164 mm x 120 mm x 112 mm	2.20 dm <sup>3</sup>	478.00 g
		carton box			

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

#### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

OSRAM is distribution partner of LEDVANCE of LAMPS



OSRAM GmbH Marcel-Breuer-Strasse 6 80807 Munich, Germany