

Ring ratchet open-ended spanner set 13 pcs. with holder (44665)

wiha 

Tools that work for you

Wiha Werkzeuge GmbH
Obertalstraße 3-7 78136 Schonach
E-Mail: info.de@wiha.com
Tel.: +49 (0)7722 959-0



Article number: 30391

Order no.: 44665

EAN: 4010995446659

Increases your efficiency: Fastening without interruption thanks to a finely toothed ring ratchet.

Simplifies your work: With a convenient holder for clearly arranged storage and easy withdrawal.

Increases your efficiency: Improved accessibility in confined spaces thanks to 15° jaw positioning.

Application: For installation and mounting work.

Eminently suitable for working in confined spaces.

Opening tightly fastened screws requires great force. With the leverage action from Wiha's ring ratchet open-ended spanner, the user can easily open any fastening. The jaw end is also excellently suited for tightening screws and nuts. With 15° jaw positioning, the jaw end is perfect for working in confined spaces. Similarly, when working with the ring ratchet, the user benefits from the fine tothing with 72 teeth, offering a short return angle and highest comfort when working in confined spaces due to the double hex design. By simply turning around its own axis, it can be switched between right and left rotation. Made of high quality chrome vanadium steel, the ring ratchet open-end spanners are distinguished by their longevity and robustness, not the least thanks to their corrosion-resistant and easy to clean surface. The set includes the 12 most commonly used sizes from 8 to 19 mm, neatly stored in a convenient holder. The holder can be opened with a single hand to remove the appropriate size. The non-slip surface finish ensures a strong grip, even in oily or wet work situations.

Based on DIN 3113

Content:

- 1x Ring ratchet open-end spanner 8 x 136 mm (44638)
- 1x Ring ratchet open-end spanner 9 x 142 mm (44639)
- 1x Ring ratchet open-end spanner 10 x 160 mm (44640)
- 1x Ring ratchet open-end spanner 11 x 168 mm (44643)
- 1x Ring ratchet open-end spanner 12 x 174 mm (44653)
- 1x Ring ratchet open-end spanner 13 x 180 mm (44654)
- 1x Ring ratchet open-end spanner 14 x 190 mm (44655)

- 1x Ring ratchet open-end spanner 15 x 200 mm (44656)
- 1x Ring ratchet open-end spanner 16 x 215 mm (44657)
- 1x Ring ratchet open-end spanner 17 x 230 mm (44658)
- 1x Ring ratchet open-end spanner 18 x 240 mm (44659)
- 1x Ring ratchet open-end spanner 19 x 248 mm (44660)
- 1x holder

Application: For installation and mounting work. Eminently suitable for working in confined spaces.

Customs tariff number 82041100
