PICK MATTOCK WITH FIBREGLASS HANDLE

Built to withstand the toughest jobs, the Roughneck pick mattock is manufactured from drop forged steel and heat treated for extra toughness. The pick mattock head combines the functions of a horizontal mattock blade and a point pick, ideal for digging in and breaking up both soft and hard ground, or dislodging stones and mortar. Mounted on a solid fibreglass handle, it is not only stronger than conventional wood, but far more durable and requires no maintenance. At 900mm/36" long, they generate significant striking force and are ideal for heavy work.

- Solid fibreglass core
- Soft grip
- Drop forged
- Heat treated
- Powder coated

IDEAL FOR: SOFT GROUND

IDEAL FOR: HARD GROUND

SOLID FIBREGLASS CORE

SOFT GRIP

DROP FORGED

HEAT TREATED

POWDER COATED

PRODUCT OVERVIEW

CODE	DESCRIPTION	SIZE	WEIGHT	BARCODE	COMMODITY CODE
64-152	Pick mattock with fibreglass handle	-	2.27kg/5lbs	0 025997 641524	82013000 00

ADDITIONAL INFORMATION

DESCRIPTION
-

SINGLE ITEM DIMENSIONS

OT CODE	LENGTH (mm)	WIDTH (mm)	HEIGHT (mm)	WEIGHT (g)
64-152	906.0	513.0	-	3540.0

PACKAGED ITEM DIMENSIONS

OT CODE	LENGTH (mm)	WIDTH (mm)	HEIGHT (mm)	WEIGHT (g)
64-152	906.0	513.0	-	3540.0

PICK MATTOCK WITH FIBREGLASS HANDLE

WASTE PACKAGING DETAILS

OT CODE	PAPER & CARD (g)	PLASTIC (g)	METAL (g)
64-152	-	-	-

INNER CARTON DIMENSIONS

OT CODE	LENGTH (mm)	WIDTH (mm)	DEPTH (mm)	NET WEIGHT (g)	GROSS WEIGHT (g)	PACK QTY
64-152	-	-	-	-	-	1

SHIPPING CARTON DIMENSIONS

OT CODE	LENGTH (mm)	WIDTH (mm)	DEPTH (mm)	NET WEIGHT (g)	GROSS WEIGHT (g)	CARTON QTY
64-152	920	148	83	3.15	4.2	1

PRODUCT SAFETY INFORMATION

WEAR EYE PROTECTION

WEAR HAND PROTECTION

WEAR FOOT PROTECTION

WARNING: ONLY USE FOR BREAKING UP GROUND. DO NOT USE TO STRIKE METAL OR FOR PRYING. DO NOT USE IF CRACKS OR DAMAGE ARE DETECTED ON THE HEAD OR HANDLE. BE AWARE OF AND AVOID BURIED POWER CABLES AND PIPES. IMPROPER USE CAN CAUSE POSSIBLE EYE OR BODILY INJURY.

GUARANTEE

This ROUGHNECK® product includes a 25-Year Guarantee. This covers faulty materials or manufacturing defects, excluding normal wear and tear, consumable parts or customer misuse. Damaged or faulty items can be returned to the place of purchase for replacement. This guarantee is in addition to and in no way prejudices the users statutory rights.