

## Tool case set XL eMobility 77-pcs.. (44198)



Wiha Werkzeuge GmbH  
Obertalstraße 3-7 78136 Schonach  
E-Mail: info.de@wiha.com  
Tel.: +49 (0)7722 959-0



**Article number:** 930073201

**Order no.:** 44198

**EAN:** 4010995441982

**Increases your safety:** Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC.

**Increases your efficiency:** A comprehensive tool assortment, always having the right tool at hand when needed.

**Increases your efficiency:** The design and function of the tool trays guarantee quick and easy access to tools.

**Dimensions:** 51,0 x 42,0 x 22,0 cm

**Application:** Huge assortment of insulated tools, compiled for work on electrical vehicles.

Working on automobiles with an electric drive requires special qualifications of the employees as well as safe, certified equipment. With the Tool case set XL eMobility, the user always has the right tool for the assembly and repair of hybrid and electric vehicles at hand. The tool case is compactly accommodated and thanks to a convincing selection of high-quality, insulated hand tools, the right tool is always available for every application. The majority of the tools offer safety when working on live parts thanks to the VDE-certified insulation. The tool inserts of the case have been designed with an eye to efficient operation so that all tools can be removed quickly and easily. The contents of the case can be secured against theft with padlocks on the integrated eyelets (these are not included in the scope of delivery). Additional storage space is provided by free lugs and extra space in the bottom tray of the case. In addition, the ergonomic two-component handle guarantees a comfortable carrying experience. The case is made of robust polypropylene and is equipped with gas pressure shock absorbers which hold the lid in various positions, prevent uncontrolled closing of the lid and thus prevent injuries to the user. From voltage testers to torque wrenches, from protective gloves to warning signs: with the fully equipped tool case, you always have the right Wiha tool at hand.

Work on electric vehicles may only be carried out by qualified and authorised specialist personnel.

DIN EN 60900

Content:

- 1x Water pump pliers Professional electric with push button adjustment 250 mm (37450)

- 1x Cable cutter Professional electric with switchable opening spring 210 mm (43662)
- 1x Professional electric diagonal cutters with DynamicJoint® 180 mm (43340)
- 1x Long flat-nose pliers Professional electric 160 mm (26732)
- 1x Needle nose pliers Professional electric with cutting edge curved shape, approx. 40° 200 mm (26729)
- 1x Combination pliers Professional electric with DynamicJoint® and OptiGrip with extra long cutting edge 200 mm (26711)
- 1x Cable stripping knife straight cutting edge for round cables in blister pack (38798)
- 1x Insulated extension 3/8" square adapter for nut driver inserts, insulated 125 mm (43057)
- 1x Insulated extension 3/8" square adapter for nut driver inserts, insulated 250 mm (43058)
- 1x slimVario® electric adapter for 1/4" nut driver 6 mm (43139)
- 1x Insulated nut driver insert 1/4" hexagon head 4 mm (43088)
- 1x Insulated nut driver insert 1/4" hexagon head 5 mm (43089)
- 1x Insulated nut driver insert 1/4" hexagon head 5.5 mm (43090)
- 1x Insulated nut driver insert 1/4" hexagon head 7 mm (43092)
- 1x Insulated nut driver insert 1/4" hexagon head 8 mm (43093)
- 1x Insulated nut driver insert 1/4" hexagon head 9 mm (43094)
- 1x Insulated nut driver insert 1/4" hexagon head 10 mm (43095)
- 1x Insulated nut driver insert 1/4" hexagon head 11 mm (43096)
- 1x Insulated nut driver insert 1/4" hexagon head 12 mm (43097)
- 1x Insulated nut driver insert 1/4" hexagon head 13 mm (43098)
- 1x Insulated nut driver insert 1/4" hexagon head 14 mm (43099)
- 1x Insulated nut driver insert 3/8" hexagon head 16 mm (43071)
- 1x Insulated nut driver insert 3/8" hexagon head 17 mm (43072)
- 1x Insulated nut driver insert 3/8" hexagon head 18 mm (43073)
- 1x Insulated nut driver insert 3/8" hexagon head 19 mm (43074)
- 1x Insulated nut driver insert 3/8" hexagon head 21 mm (43075)
- 1x Insulated nut driver insert 3/8" hexagon head 22 mm (43076)
- 1x Flashlight with LED, laser and UV light in blister pack, including 3 AAA batteries 100 - 310 lm (41286)
- 1x Screwdriver SoftFinish® electric slimFix Slotted 3.5 x 100 mm (35446)
- 1x Screwdriver SoftFinish® electric slimFix Slotted 4 x 100 mm (35390)
- 1x Screwdriver SoftFinish® electric slimFix Slotted 5.5 x 125 mm (35391)
- 1x Screwdriver SoftFinish® electric slimFix Slotted 6.5 x 150 mm (35392)
- 1x Screwdriver SoftFinish® electric slimFix Phillips PH1 x 80 mm (35393)
- 1x Screwdriver SoftFinish® electric slimFix Phillips PH2 x 100 mm (35394)
- 1x Screwdriver SoftFinish® electric slimFix TORX® T20 x 100 mm (36538)
- 1x Screwdriver SoftFinish® electric slimFix TORX® T25 x 125 mm (36539)
- 1x Screwdriver SoftFinish® electric slimFix TORX® T27 x 125 mm (36540)
- 1x Screwdriver SoftFinish® electric slimFix TORX® T30 x 125 mm (36541)
- 1x Screwdriver SoftFinish® electric slimFix TORX® T40 x 150 mm (36542)
- 1x Screwdriver SoftFinish® electric Hex nut driver 7 x 125 mm (00858)
- 1x Screwdriver SoftFinish® electric Hex nut driver 8 x 125 mm (00859)
- 1x Screwdriver SoftFinish® electric Hex nut driver 10 x 125 mm (00861)
- 1x Screwdriver SoftFinish® electric Hex nut driver 13 x 125 mm (00864)
- 1x Torque screwdriver set TorqueVario®-S electric Mixed, variably adjustable torque limit, 14 pcs. incl. folding bag (40674)
- 1x Torque key, electric 3/8" for nut drivers, variably adjustable torque limit 290 mm (44163)
- 1x Adapter electric for 1/4" socket wrench 100 mm (44355)
- 1x Adapter TorqueVario-S electric for 1/4" nut driver 178 mm (43128)
- 1x Insulated nut driver insert 1/4" hexagon head 6 mm (43091)
- 1x Socket wrench insert electric deep 3/8" Double hex 8 (44146)
- 1x Socket wrench insert electric deep 3/8" Double hex 10 (44147)
- 1x Socket wrench insert electric deep 3/8" Double hexagon 12 (44148)
- 1x Insulated nut driver insert 1/4" internal hexagon 4 mm (43110)
- 1x Insulated nut driver insert 1/4" internal hexagon 6 mm (43112)
- 1x Insulated nut driver insert 1/4" internal hexagon 8 mm (43113)
- 1x Tool case XL empty

**Application:** Huge assortment of insulated tools, compiled for work on electrical vehicles.

---

Customs tariff number 82060000

---

VDE article Yes

---

